



FEATURES:

- ✓ Converts BNC (male) cables / connectors to alligator test clips for test versatility.
- ✓ BNC connector is molded directly to the wire for pull strength durability and dust and moisture resistance.
- ✓ BNC center contact is gold plated Beryllium Copper for corrosion resistance, low contact resistance and long insertion life.
- ✓ Alligator clips attach to terminals up to .300" (7.6mm) diameter.
- ✓ Black wire is connected to BNC shell, red wire to BNC center contact.

MATERIALS:

BNC: Nickel Plated Brass, *Center Contact:* Gold Plated Beryllium Copper

Dielectric: PTFE

Wire: 18 AWG, PVC Insulated

Alligator: Nickel plated steel, *Spring:* stainless steel

Boot: Vinyl, color matches color of wire.

RATINGS:

Operating Voltage: Hands free testing in controlled voltage environments: 150 VRMS Max.

Operating Temperature: +122°F (+50°C) Max.

ORDERING INFORMATION: Model 2630*

* Custom lengths are available, contact Pomona Product Support at: 1-800-241-2060

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02"$ (.51 mm), .xxx = $\pm .005"$ (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Sales: 800-490-2361 Fax: 888-403-3360 Technical Assistance: 800-241-2060
For "Where to Buy" information, visit the Pomona web site at www.pomonaelectronics.com