



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Internet Office 300VA Ultra-compact Standby 120V UPS

MODEL NUMBER: **INTERNETOFFICE300**



Highlights

- 300VA ultra-compact 120V standby UPS
- Maintains AC output during power failures
- 3 UPS battery supported outlets, 3 surge-only outlets
- TEL/DSL/ethernet protection
- NEMA 5-15P input plug and 6 NEMA 5-15R outlets

Package Includes

- INTERNETOFFICE300 UPS System
- Phone cable
- Instruction manual

Description

Tripp Lite's INTERNETOFFICE300 UPS System provides complete power protection for your entire computer set-up. 300 VA power capacity maintains your Internet connection allowing you to work online through short blackouts or safely shut down during longer ones. Unique design features 6 outlets (3 UPS & surge + 3 surge-only outlets) and diagnostic LEDs. Built-in RJ45 jacks prevent surges from damaging your modem/fax/10BT equipment. A 6-ft. telephone cord is also included. \$100,000 [Ultimate Lifetime Insurance](#) (USA & Canada Only) covers connected equipment.

Features

- 300 VA output power rating (150 watts)
- Up to 11 minutes backup time (single PC; 15-in monitor)
- Battery run time: 10 minutes half load/4 minutes full load
- 6 protected outlets (3 UPS & surge + 3 surge-only outlets); 6-ft. cord
- Built-in RJ45 jacks prevent surges from damaging your modem/fax/10BT equipment; 6-ft. telephone cord included
- Complete surge protection and EMI/RFI noise filtering
- \$100,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico, & Canada Only) covers connected equipment
- 5 diagnostic LEDs indicate AC present, line fault, on battery, overload and battery low/replace
- Optional PDUB15 bypass PDU enables hot-swappable UPS replacement with no disruption to connected equipment

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	300
Output Watt Capacity (watts)	150
Nominal Output Voltage(s) Supported	120V



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Frequency compatibility	50 / 60 Hz
Output voltage regulation (Battery mode)	+/- 5%
Built-in UPS output receptacles	6 5-15R outlet(s)
Surge suppression only outlets	3 UPS outlets, 3 surge-only outlets
Output circuit breaker	15A
Hot-Swap PDU options	PDUB15 (2U / 8 5-15R outlets)
Output AC waveform (AC mode)	Sine wave
Output AC waveform (battery mode)	PWM sine wave
INPUT	
Rated input current (at maximum load)	12A
Nominal Input Voltage(s) Supported	120V AC
UPS input connection type	5-15P
UPS Input cord length (ft.)	6
UPS Input cord length (m)	1.8
Recommended Electrical Service	15A 120V
Input cord length (ft.)	6
Input cord length (m)	1.8
Phase	Single-Phase
BATTERY	
Full load runtime (minutes)	4 min. (150w)
Half load runtime (minutes)	10 min. (75w)
DC system voltage (VDC)	12
LEDS ALARMS & SWITCHES	
LED Indicators	5 LEDs indicate complete UPS operational status
Switches	Power off / on switch
SURGE / NOISE SUPPRESSION	
UPS AC suppression joule rating	380
UPS AC suppression response time	Instantaneous
UPS Dataline suppression	1 line TEL/DSL (1 in / 1 out); 10/100Base T Ethernet
EMI / RFI AC noise suppression	Yes
AC suppression joule rating	380



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

AC suppression response time	Instantaneous
Dataline suppression	1 line TEL / DSL or 10Base T Ethernet protection
PHYSICAL	
Installation form factors supported with included accessories	Tower; Ultra-compact desktop
Primary form factor	Desktop
UPS / Power Module dimensions in primary form factor (height x width x depth / inches)	2.6 x 11 x 4.5
UPS / Power Module dimensions in primary form factor (height x width x depth / cm)	6.7 x 27.9 x 11.4
UPS / Power Module weight (lbs)	4
UPS / Power Module weight (kg)	1.8
UPS Shipping dimensions (height x width x depth / inches)	4.5 x 13 x 8.2
UPS Shipping dimensions (height x width x depth / cm)	11.4 x 33 x 21
Shipping weight (lbs)	5.4
Shipping weight (kg)	2.5
UPS housing material	ABS
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC mode BTU / hr. (full load)	32.6
Battery mode BTU / hr. (full load)	44.3
AC mode efficiency rating (100% load)	94%
LINE / BATTERY TRANSFER	
Transfer time	2-4 milliseconds
Low voltage transfer to battery power (setpoint)	99V
High voltage transfer to battery power (setpoint)	141V
SPECIAL FEATURES	
Green & high efficiency features	Greater than 95% efficiency - GREEN UPS



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI)
WARRANTY	
Product Warranty Period (U.S. & Canada)	3-year limited warranty
Product Warranty Period (Latin America)	3-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	3-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$100,000 Ultimate Lifetime Insurance

Related Items

Optional Products

Model Number	Description	Qty.
WEXT5-INTERNET	5-Year Extended Warranty - For Internet Office, AVR and ECO Series UPS Systems	1
PDUB15	Single-Phase Hot-Swap PDU, 1.4kW 15A 120V, 2U Horizontal Rackmount, 8 NEMA 5-15R outlets, set of 2 NEMA 5-15P input plugs	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at:

<http://www.tripplite.com/sku/INTERNETOFFICE300>.

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[INTRNT OFFC300](#)