


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	P	F	REVISIONS					
G	14			ZONE	LTR	DESCRIPTION	DATE	APPD	
					F	EC 0720-0279-93	6-21-93	SSG BB	

AMP
WIRE RANGE
4/0 AWG
STRANDED

METRIC
DIMENSIONS LISTED IN mm [INCHES]

1. TONGUE MATERIAL THK 2.59±0.08[.102±.003]
FOR 19.43 [.765] MAX WIRE INS DIA



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

MAX RECOMMENDED OPERATING TEMPERATURE: 105°c
VOLTAGE RATING: -
CIRCULAR MIL AREA: 96.3-117mm² [190,000-231,100] STRANDED

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON:
2 PLC DEC ± 0.20[.008]
3 PLC DEC ± -
ANGLES ± -
MATERIAL
COPPER PER ASTM B-152
NYLON (MIL-M-20693) TYPE 1
COLOR: BLUE
FINISH
TIN PLATE PER MIL-T-10727

-		LOOSE PC		329150	
QTY		PACKAGE TYPE		PART NO	
DR 6-21-93 S.S. GOULDEN		AMP AMP Incorporated Harrisburg, PA 17105-3608			
CHK 6-21-93 R. HERSEY					
APPD 6-21-93 B. BARE		NAME TERMINAL, RING TONGUE, TERMINYL WIRE SIZE: 4/0 AWG			
APPD 6-21-93 M. ELLIS					
PRODUCT SPEC -		SIZE B CAGE CODE 00779 DRAWING NO C-329150			
APPLICATION SPEC -					
WEIGHT -		SCALE NTS		SHEET 1 OF 1	