


Ring Tongues – Vinyl Insulated Butted Seam 12-10 AWG




| Product Number† | UPC (054007-) | Wire Range (AWG) | Stud Size | W    | C    | L    | E    | Thickness | Barrel Length | Barrel I.D. | Maximum Insulation Diameter | Terminals per Case |
|-----------------|---------------|------------------|-----------|------|------|------|------|-----------|---------------|-------------|-----------------------------|--------------------|
| MVU10-4R/SK     | 01946         | 12-10            | 4         | 0.28 | 0.29 | 0.98 | 0.84 | 0.040     | 0.25          | 0.135       | 0.250                       | 500                |
| MVU10-6RK       | 01948         | 12-10            | 6         | 0.38 | 0.29 | 1.03 | 0.84 | 0.040     | 0.25          | 0.135       | 0.250                       | 500                |
| MVU10-8RK       | 01950         | 12-10            | 8         | 0.38 | 0.29 | 1.03 | 0.84 | 0.040     | 0.25          | 0.135       | 0.250                       | 500                |
| MVU10-10RK      | 01951         | 12-10            | 10        | 0.38 | 0.29 | 1.03 | 0.84 | 0.040     | 0.25          | 0.135       | 0.250                       | 500                |
| MVU10-14R/SK    | 01952         | 12-10            | 1/4       | 0.53 | 0.44 | 1.26 | 0.99 | 0.040     | 0.25          | 0.135       | 0.250                       | 500                |
| MVU10-516R/SK   | 01954         | 12-10            | 5/16      | 0.53 | 0.44 | 1.26 | 0.99 | 0.040     | 0.25          | 0.135       | 0.250                       | 500                |
| MVU10-38R/SK    | 01956         | 12-10            | 3/8       | 0.54 | 0.44 | 1.26 | 0.99 | 0.040     | 0.25          | 0.135       | 0.250                       | 500                |




MVU10-4R/S  
4  
12-10


Stud Size  
Wire Range




MVU10-6R  
6  
12-10



MVU10-8R  
8  
12-10




MVU10-10R  
10  
12-10




MVU10-14R/S  
1/4  
12-10

Stud Size  
Wire Range



MVU10-516R/S  
5/16  
12-10



MVU10-38R/S  
3/8  
12-10