




**Distribution-connector 1 - 24-pole,
plug-side 4 mm²,
with 5 flat plugs 6,3 x 0,8 each pole
(screw-side 2,5 mm²)**

Casing : polyamide
Contact-part : zinc-plated steel
Screw : M 4 zinc-plated steel

This connector is available in 1 - 24-pole. Each solid contact offers 5 push wire connections and can be equipped with 1 screw-type terminal each. This connector is available in other thermoplastic materials. Article-no. and weights are without screw terminals.




Shunts can be supplied as an option, separately of factory-mounted.



17,5 A
450V

PTI 250

T110



No. of poles	Length	Article-no.	Fixing	Colour	kg/100 pcs.	Pkg. qty.
1	30,0	1195350001	-	natural	1,5	250
2	41,0	1195350002	-	natural	2,2	200
3	52,0	1195350003	-	natural	2,9	200
4	63,0	1195350004	-	natural	3,5	100
5	74,0	1195350005	-	natural	4,2	100
6	85,0	1195350006	-	natural	4,9	100
7	96,0	1195350007	-	natural	5,5	100
8	107,0	1195350008	-	natural	6,2	50
9	118,0	1195350009	-	natural	6,9	50
10	129,0	1195350010	-	natural	7,5	50
11	140,0	1195350011	-	natural	8,2	50
12	151,0	1195350012	-	natural	8,9	50
13	162,0	1195350013	-	natural	9,6	50
14	173,0	1195350014	-	natural	10,2	25
15	184,0	1195350015	-	natural	10,9	25
16	195,0	1195350016	-	natural	11,6	25
17	206,0	1195350017	-	natural	12,3	25
18	217,0	1195350018	-	natural	13,0	25
19	228,0	1195350019	-	natural	13,7	25
20	239,0	1195350020	-	natural	14,4	25
21	250,0	1195350021	-	natural	15,1	25
22	261,0	1195350022	-	natural	15,8	25
23	272,0	1195350023	-	natural	16,5	25
24	283,0	1195350024	-	natural	17,2	25

