




Switches > Push Button Switches



Configuration (Pole-Throw): **Double Pole - Double Throw**

Push Button Switch Product Type: **Anti-Vandal Switch**

Number of Actuators: **Single**

Actuator Profile: **Flush**

Bushing Style: **Threaded**

Features

Product Type Features

Switch Connection Type	Wire Lugs
Push Button Switch Product Type	Anti-Vandal Switch
Illuminated	With
Actuator Style	Round Actuator

Configuration Features

Configuration (Pole-Throw)	Double Pole - Double Throw
Number of Actuators	Single
Snap Action	Without
Support Bracket	Without
Switch Feedback Type	Auditory
Operating Function	Push-On/Push-Off

Electrical Characteristics

Contact Current Rating	3 A
Operating Voltage Range	250 VAC

Body Features

Case Material	PBT
Product Orientation	Vertical



Actuator Force	357 g[12.6 oz]
Actuator Profile	Flush
Bushing Style	Threaded

Contact Features

Switch Contact Plating Material	Silver
---------------------------------	--------

Housing Features

Process Sealed	Yes
----------------	-----

Dimensions

	22 in
--	-------

Industry Standards

IP Rating	IP67
-----------	------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量超出标准 Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (4% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2213772-5
AV22 SPM 3A MOVE RING LED RED 12V

TE Part # 5-2213772-5
AV22 DPM 3A MOVE RING LED GREEN 24V

TE Part # 1-2213772-3
AV22 SPM 3A MOVE RING LED GREEN 12V

TE Part # 1-2213772-7
AV22 SPM 3A MOVE RING LED BLUE 12V

TE Part # 2213771-1
AV22 SPM 3A NO LED

Also in the Series | ALCOSWITCH AV22

Anti-Vandal Switches(124)

Push Button Switches(124)

Customers Also Bought

TE Part #HD10-9-1939PE-B022
REC, 9P, BLK, E, PANEL, J1939, TYPE 1

TE Part #3-1617029-3
HFW1131K04M = M39016/6-107M


TE Part #1-1617118-9
J1MACD-26XL = M39016/23-030L

TE Part #1617168-3
JMSCT-18XL = M28776/3-037L







TE Part #1-2007637-5
SFP+ assy 2x2 EMI Sprg 4 LP Sn
Enhanced



TE Part #8-2176363-7
RQ 0402 3K4 0.1% 10PPM 5K RL



TE Part #2213771-7
AV22 DPL 3A NO LED



TE Part #5-2213772-5
AV22 DPM 3A MOVE RING LED
GREEN 24V



TE Part #2-2435260-1
HCP16A, Std Force, 0.187 Term.Sht
Roller



TE Part #5747845-5
15 MSFL RCPT RA 318 (SL,FM,BL)

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_7-2213772-9_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_7-2213772-9_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_7-2213772-9_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ALCOSWITCH Anti-Vandal Switch

English

Agency Approvals

UL Report

English