




Fxx^{*1)}PA-K700
e.g. F15PA-K700

*1) xx No. of contacts 09, 15, 25 or 37

xx	A [mm]	B [mm]	C [mm]
09	30.8	16.9	25
15	39.1	25.2	33.3
25	53	38.9	47.04
37	69.3	55.3	63.5

Protection standard IP67, 100% checked according to DIN 40050

RoHS compliant

3	xx	Signal contact	P0 / Brass	AuroPur / AWG 20
2	1	Shell	Brass	tin plated
1	1	Insulator	PBT (-25°C - +70°C)	red
No.	St.	Part	Type Description/Material	Surface plating/Colour/Class
TITLE				
SCALE				
ISO 2768-m 2:1				
NAME / DATE				
sschref 22-05-2013				
DRAWN				
CHECKED				
A. Denzinger 22-05-2013				
DWG.NO.				
FxxPA-K700				
REV.				
1				
PAGES				
1				
REPLACEMENT FOR:				
ORIGINAL DIN A3 DRAWING AS A FILE				
DATE				
CH.-NO.				
REV.				
1				
FCT group				
fctgroup.com				
Waterproof				
D-Sub Miniature Connector				