

37" Class Viera® C22 Series 720p LCD

FIND ANOTHER MODEL

Model number: TC-L37C22

Print this

 |

Share this

Product no longer available for purchase.

37" Class Viera® C22 Series 720p LCD (37.0" Diagonal)

- IPS Panel
- VIERA Image Viewer™
- VIERA Link™
- ENERGY STAR Qualified

Online Order Assistance

- [Track your order](#)
- [Print your invoice](#)
- [Read our shipping FAQs](#)
- [Register your product](#)

Accessories

- [Find accessories for your product](#)

Contact Us

- [Live Chat](#)
- [Phone](#)
- [Email](#)
- [Mail](#)
- [International Support](#)

Operating Manuals	Help & Tutorials	FAQs	Tech Specifications	Warranty & Care Plans	Accessories	Drivers & Downloads
Model Type		LCD				
Series		C22				
Model Year		2010				
VIDEO						
Screen Size		37" Class (37.0" diagonal)				
Viewing Angle		178°				
Aspect Ratio		16:9				
Native Resolution (Number of Pixels)		1,049,088 (1,366 x 768)				
HDTV Display Capability (1080p, 1080i, 720p)		720p				
EDTV Display Capability (480p)		Yes				
Aspect Control		480i/p: Full, Just, 4:3, Zoom 1080i/p: Full, H-Fill, Just, 4:3, Zoom				
Panel		IPS (WXGA)				
Filter		Fine Black Panel				
Backlight		EEFL				
Progressive Scan		Yes				
24p Playback(2:3)		Yes				
Intelligent Scene Controller		Yes				
Motion Focus Technology		No				
Contrast (Dynamic)		18,000:1				
120 Hz		No				
24p Smooth Film		No				
AUDIO						
Speakers		Full-range x 2 (L, R)				
Number of Speakers		2				
Audio Output		20 W (10% THD)				
Surround Sound		Yes				
INPUTS & JACKS						
Integrated ATSC Tuner		Yes				
VIERA Image Viewer™		Y (JPEG playback)				
HDMI Input		2				
Analog Audio Input (for HDMI)		Yes				
Composite Video Input		2 (1 side)				
Audio Input (for Video)		2 (1 side)				
PC Input		1				
Component Video Inputs (Y, PB, PR)		1				
Audio Input (for Component Video)		1				
Digital Audio Output		1 (5.1 ch)				
HDMI Input-Support Feature		Audio Return Channel (Input 1)				
CONVENIENCE						
VIERA Link™		Yes				
Universal Dock for iPod		No				
VIERA® Tools		Yes				
Game Mode		No				
Clean Touch Bezel		No				
Built-In Closed Caption Decoder		Yes				
Off - Timers		Yes				
Trilingual Menu		English/Spanish/French				
GENERAL						
Power Supply		AC 110 - 127 V, 60 Hz				
Rated Power Consumption		149 W				
Standby Power Consumption		0.3 W				
On Mode Average Power Consumption		71.4 W				
Energy Star		Yes				
Receiving System		ATSC/QAM/NTSC				
Operating Temperature		32°F - 104°F (0°C - 40°C)				
Safety Standard		UL6500/C-UL				
Swivel Angle		No				
Tilt Angle		No				
VESA Compatible		Yes				
Optional Wall-mounting Bracket		TYWK3L2RW				
SPECIFICATIONS						
Dimensions (H x W x D) with Stand		24.4" x 36.0" x 11.3"				
Dimensions (H x W x D) without Stand		22.8" x 36.0" x 3.9"				
Weight (lbs.) w/Stand		34.2 lbs.				
Weight (lbs.) without Stand		29.8 lbs.				
Carton Dimensions		26.1" x 49.4" x 7.5"				
Gross Weight [lbs (kg)]		39.7 lbs. (18.0 kg)				
Weight		39.7 lbs.				