



Select a Category

GO

REGULAR-POINT 118° HIGH-SPEED DRILL BITS

[Product Index](#) > [Drill Bits and Hole Saws](#) > [Drill Bits](#) > [Regular-Point 118° High-Speed Drill Bits](#) > 53122

Regular-Point 118° High-Speed Drill Bit - 13 / 32" Bit Size

- General-purpose, high-speed bit for reliable performance in a wide range of materials.
- Standard jobber length.
- Black-oxide finish reduces chip welding.
- Lightly roughened surface has higher lubricity for easier chip flow.



Buy Now!

Pictured: 53128

Cat. No.	Bit Size	Flute Length	Overall Length	Weight (lbs.)
53122	13/32"	3-7/8" (98)	5-1/4" (133)	.15

All dimensions are in inches and (millimeters) except where indicated.

Download High-Resolution .jpg photo

Download High-Resolution .eps photo



The downloadable files are compressed in .zip format to save on downloading times.
Decompressing .zip files requires applications such as [WinZip](#) for the PC and [Stuffit Expander](#) for the Macintosh.

 **WARNINGS:** Always ensure that you and persons in the vicinity wear approved eye protection.

 **WARNINGS:** Never use on or near live electrical circuits.

For questions regarding Klein Tools, please use the [Contact Klein Tools](#) page. For questions regarding Klein Tools' policy regarding the use of this site, please see our [Legal Notice/Privacy Statement](#).