

D-SUB connector set - VS-09-SET-STD - 1689145

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

D-SUB connector set, shell size 1, IP67 degree of protection



Key commercial data

Packing unit	1 pc
Weight per Piece (excluding packing)	55.9 GRM
Custom tariff number	85366990
Country of origin	Germany

Technical data

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 80 °C

General

Type	D-SUB 9
Degree of protection	IP67
Inflammability class according to UL 94	V0
Cable exit	Angled
Housing material	PA
Seal material	Flat gasket: NBR; profile gasket: EPDM
Ambient temperature (operation)	-40 °C ... 80 °C

Classifications

eCl@ss

eCl@ss 4.0	27140816
------------	----------

D-SUB connector set - VS-09-SET-STD - 1689145

Classifications

eCl@ss

eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27261203
eCl@ss 7.0	27440202
eCl@ss 8.0	27440202

ETIM


ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501


Drawings

Dimensioned drawing



D-SUB sleeve housings


Dimensioned drawing



D-SUB panel mounting frame

D-SUB connector set - VS-09-SET-STD - 1689145

Dimensioned drawing



Panel cutout