


ESKA Fuses

■Product Dimensions(mm)

Part Number	A	B	C	D
	Max.	Max.	Max.	Max.
LP-MSM010	4.73	3.41	0.81	0.60
LP-MSM014	4.73	3.41	0.81	0.60
LP-MSM020	4.73	3.41	0.81	0.60
LP-MSM050	4.73	3.41	0.61	0.60
LP-MSM075	4.73	3.41	0.61	0.60
LP-MSM110	4.73	3.41	0.61	0.60
LP-MSM125	4.73	3.41	1.25	0.60
LP-MSM150	4.73	3.41	1.25	0.60
LP-MSM160	4.73	3.41	1.25	0.60
LP-MSM190	11.51	5.33	0.55	0.60
LP-MSM200	4.73	3.41	1.25	0.60
LP-MSM260	4.73	3.41	2.25	0.60



■Part Marking System



■Electrical Characteristics

Part Number	I_H	I_T	V_{max}	I_{max}	T_{trip}		P_{dtyp}	R_{min}	R_{1max}
	(A)	(A)	(V)	(A)	Current(A)	Time(S)	(W)	(Ω)	(Ω)
LP-MSM010	0.10	0.20	60.0	10	1.5	0.15	1.0	0.700	6.000
LP-MSM014	0.14	0.34	60.0	10	1.5	0.15	1.0	0.700	6.000
LP-MSM020	0.20	0.40	30.0	10	6.0	0.06	1.0	0.600	5.000
LP-MSM050	0.50	1.00	15.0	40	8.0	0.15	1.0	0.150	1.000
LP-MSM075	0.75	1.50	13.2	40	8.0	0.20	1.0	0.100	0.480
LP-MSM110	1.10	2.20	6.0	40	8.0	0.30	1.0	0.040	0.260
LP-MSM125	1.25	2.50	6.0	40	8.0	0.40	1.0	0.070	0.250
LP-MSM150	1.50	3.00	6.0	40	8.0	0.50	1.0	0.040	0.110
LP-MSM160	1.60	2.80	6.0	40	8.0	1.00	1.0	0.030	0.100
LP-MSM190	1.90	3.80	16.0	100	10.0	2.00	1.5	0.024	0.080
LP-MSM200	2.00	3.50	6.0	40	8.0	2.00	1.0	0.020	0.060
LP-MSM260	2.60	5.20	6.0	40	8.0	2.50	1.0	0.015	0.047