






⊗ = Assmann Logo

RoHS
Compliant

ITEM NO

A-DIO-FS/0x-R

TITLE Mini-DIN Jack, Socket, Full Shielded - 5 sides,
3,4,5,6,7 & 8 Pin

Materials:

- Insulator: P.B.T. & 15%Glass Fiber, UL94V-0
- Contacts: Brass
- Sheel: Brass
- Sheel Plating: Nickel Plated

Contact Plating:

- Underplate: 50μ" Nickel
- Contact Area: 80μ"~100μ" Tin/Lead or
80μ"~100μ" Tin/Lead Free

Electrical:

- Current Rating: 100V AC 1Amps Max.
12V DC 2amps Max.
- Contact Resistance: 30MΩ Max.
- Insulation Resistance: 500MΩ Min. at 500V DC
- Dielectric Withstanding: 500V AC at 1 Minute
- Operating Temperature: -40°C ~ +75°C

ASSMANN
Electronics, Inc.

1840 W. Drake Drive, Suite 101 - Tempe, AZ 85283

Toll Free: 1-877-277-6266 Email: info@usa-assmann.com

THIS DRAWING IS UNPUBLISHED
© Copyright 2009 by Assmann Electronic Components
All International Rights Reserved