

Crimping pliers - CRIMPFOX-RC 6 - 1212710

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimping pliers, for uninsulated cable lugs, 0.5 - 6 mm², indent crimp

Product Features

- ✓ Crimping pliers for uninsulated cable lugs
- ✓ Compact and lightweight design
- ✓ Marked die stations for precise processing of corresponding cross sections
- ✓ Unlockable pressure lock
- ✓



Key commercial data

Packing unit	1 pc
Custom tariff number	82032000
Country of origin	Sweden

Technical data

Dimensions

Length (b)	198 mm
Height	59 mm
Width (a)	18 mm

General

Compression	Indent crimp
Type of contact	Non-insulated cable lugs
Designation	Crimping position 1
Min. cross section	0.5 mm ²
Max. cross section	2.5 mm ²

Crimping pliers - CRIMPFOX-RC 6 - 1212710

Technical data

General

AWG min	20
AWG max	14
Designation	Crimping position 2
Min. cross section	4 mm ²
Max. cross section	6 mm ²
AWG min	12
AWG max	10

Classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811

ETIM

ETIM 3.0	EC001186
ETIM 4.0	EC000168
ETIM 5.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518