




MICRO SWITCH
FREEPORT ILLINOIS U.S.A.
A DIVISION OF HONEYWELL
FED MFG CODE 81928

SWITCH-TOGGLE

CATALOG LISTING
12TW887
SERIES CHART 1

CATALOG LISTING	AVAILABLE LOCKING COMBINATIONS FOR CONFIGURATION SEE LETTERED DETAILS	CIRCUIT MADE WITH TOGGLE LEVER IN			ELECTRICAL DATA
		KEYWAY SIDE (1-2, 4-5)	CENTER (1-2, 4-5)	OPPOSITE KEYWAY (2-3, 5-6)	
12TW887-1	A,B,D,E,F,G,H,I,K,L,M,N,P	ON	OFF	ON	L 117 5A-125 VAC RJ Ⓢ
12TW887-2	D, F, G	OFF	NONE	ON	
12TW887-3	D, F, G	ON	NONE	ON	
12TW887-21	E, F, K, M	NONE	OFF	ON	
12TW887-31	E, F, K, M	NONE	ON	ON	
12TW887-4	F	MOM OFF	NONE	ON	
12TW887-5	E, F, K, L, M, N	MOM ON	OFF	ON	
12TW887-6	F	MOM ON	NONE	OFF	
12TW887-7	E, L, N	MOM ON	OFF	MOM ON	
12TW887-8	F	MOM ON	NONE	ON	
12TW887-41	F	NONE	MOM OFF	ON	
12TW887-51	E	NONE	ON	MOM ON	
12TW887-61	E	MOM ON	OFF	NONE	



- NOTES
- 1 FURNISHED UNASSEMBLED
 - 2 SUFFIX MUST BE ADDED FOR DESIRED TYPE TOGGLE LOCKING
 - 3- TERMINALS ARE PLATED FOR SOLDERING
 - 4 NICKEL PLATED MATTE FINISH
 - 5- GOLD PLATED CONTACTS

THIRD ANGLE PROJECTION			
SCALE 2 TO 1			
DO NOT SCALE PRINT			
TOLERANCES			
APPLY TO DIMENSION UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED TOLERANCES ARE:			
DIM	TOL	DIM	TOL
mm	mm/in	in	mm/in
NO PLACES	X	1/64	0.0005
ONE PLACE	XX	0.0015	0.0005
TWO PLACES	XXX	0.0025	0.0005
THREE PLACES	XXXX	0.0005	0.0005
ANGLES			
SI METRIC		US CUSTOMARY	
DESIGN UNITS		WEIGHT .045 LB MAX	