



(1,27mm) .050"

DWM, HDWM SERIES

HDWM-20-58-G-S-427

HDWM-24-59-L-S-300-SM

DWM-08-56-L-D-312-SM

DWM-06-54-G-D-360

# MICRO BOARD STACKER

## SPECIFICATIONS

### DWM

For complete specifications see [www.samtec.com?DWM](http://www.samtec.com?DWM)

#### Insulator Material:

Top: Black LCP  
Bottom: Natural LCP

#### Terminal Material:

Phosphor Bronze

#### Plating:

Au or Sn over

50µ" (1,27µm) Ni

#### Current Rating:

1A

#### Operating Temp Range:

-55°C to + 105°C with Tin

-55°C to + 125°C with Gold

#### RoHS Compliant:

Yes

### HDWM

For complete specifications see [www.samtec.com?HDWM](http://www.samtec.com?HDWM)

Same as DWM except not CSA rated.

#### Processing:


Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0,15mm) .006" max

Mates with:  
SMS, SLM, RSM



Variable stacker height

Ideal for high density "skyscraper" board stacking

Choice of Surface mount or Through-hole

| TYPE STRIP | NO. PINS PER ROW                                                                     | LEAD STYLE                           | PLATING OPTION                                                   | ROW OPTION                | STACKER HEIGHT                                                         | OTHER OPTION                                                                                                                       |
|------------|--------------------------------------------------------------------------------------|--------------------------------------|------------------------------------------------------------------|---------------------------|------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------|
|            | <b>01 thru 50</b>                                                                    | Specify <b>LEAD STYLE</b> from chart | <b>-L</b><br>= 10µ" (0,25µm)<br>Gold contact, Matte Tin on tail  | <b>-S</b><br>= Single Row | <b>-“XXX”</b><br>= Stacker Height<br>Example:<br>-250 = (6,35mm) .250" | <b>-“XXX”</b><br>= Polarized Position<br>(Specify position of omitted pin)                                                         |
|            |                                                                                      |                                      | <b>-G</b><br>= 10µ" (0,25µm)<br>Gold on post, Gold flash on tail | <b>-D</b><br>= Double Row |                                                                        |                                                                                                                                    |
|            | <b>DWM</b><br>= Standard Board Spacer<br><br><b>HDWM</b><br>= High Temp Board Spacer |                                      |                                                                  |                           |                                                                        | <b>- SM</b><br>= Surface Mount<br>(Requires HDWM. 02 thru 40 positions only.)                                                      |
|            |                                                                                      |                                      |                                                                  |                           |                                                                        | <b>- A</b><br>= Alignment Pin<br>(Requires HDWM. 6 positions min -D only.)<br>Metal or plastic at Samtec discretion (N/A with -LC) |
|            |                                                                                      |                                      |                                                                  |                           |                                                                        | <b>- LC</b><br>= Locking Clip<br>(Requires HDWM. 5 positions min. -D only.)<br>(N/A with -A) (Manual placement required)           |
|            |                                                                                      |                                      |                                                                  |                           |                                                                        | <b>- P</b><br>= Pick & Place Pad<br>(Requires HDWM)                                                                                |

| LEAD STYLE | OAL           |               |
|------------|---------------|---------------|
|            | THROUGH-HOLE  | SURFACE MOUNT |
| -01        | (11,43) .450  | (8,38) .330   |
| -51        | (10,41) .410  | —             |
| -52        | (10,80) .425  | —             |
| -53        | (12,83) .505  | (9,78) .385   |
| -54        | (14,10) .555  | (11,05) .435  |
| -55        | (15,49) .610  | (12,45) .490  |
| -56        | (15,88) .625  | (12,83) .505  |
| -57        | (16,51) .650  | (13,46) .530  |
| -58        | (17,91) .705  | (14,86) .585  |
| -59        | (19,18) .755  | (15,62) .615  |
| -60        | (20,96) .825  | —             |
| -61        | (26,67) 1.050 | —             |

Diagram illustrating the dimensions and configurations for the Micro Board Stacker, including lead styles (01, 02, 01, 02) and stacker heights (01, 02, 01, 02).

**Note:** Other Gold plating options available. Contact Samtec.

**Note:** These Series are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

[WWW.SAMTEC.COM](http://WWW.SAMTEC.COM)

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 SAMTEC SILICON VALLEY • Tel: 408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: 1-800-726-8329  
 SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA • Tel: (+55 31) 3786 3227 SAMTEC UNITED KINGDOM • Tel: 44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0  
 SAMTEC FRANCE • Tel: 33 01 60 95 06 60 SAMTEC ITALY • Tel: 39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46-84477280 SAMTEC BENELUX • Tel: 44 01236 739292  
 SAMTEC ISRAEL • Tel: 972-3-7526600 SAMTEC INDIA • Tel: +91-80-3272 1612 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 SAMTEC JAPAN • Tel: 045-475-1385 SAMTEC CHINA • Tel: 86-21-6083 3766  
 SAMTEC TAIWAN • Tel: 886-2-2735-6109 SAMTEC HONG KONG • Tel: 852-26904858 SAMTEC KOREA • Tel: 82-31-717-5685 SAMTEC ANZ • Tel: 613 9580 0683