






# COVER ORIENTATION



# SECTION DD



| mat'l. code |          |     |          | tolerances unless otherwise specified |        | CUSTOMER COPY |          | <b>BERG</b><br>ELECTRONICS |                       |
|-------------|----------|-----|----------|---------------------------------------|--------|---------------|----------|----------------------------|-----------------------|
| ltr         | ecr      | no  | dr       | date                                  | linear | projection    |          | title                      | POLARIZED QUICKIE III |
|             |          |     |          |                                       | angles |               |          |                            | FEMALE DUAL BUMPS     |
|             |          |     |          |                                       | dr     | P. NIZZI      | 94 04 13 |                            | 0.38 μm / 15 μ" GOLD  |
|             |          |     |          |                                       | enrg   | JM PHAMVAN    | 94 04 13 | product family             |                       |
|             |          |     |          |                                       | chr    | P. NIZZI      | 94 04 13 | size dwg no                | 213                   |
|             |          |     |          |                                       | appd   | JM PHAMVAN    | 94 04 13 | scale                      | 4:1                   |
| A           | F40262   | PNZ | 94 04 13 |                                       |        |               |          | A3                         | 93692                 |
| sheet       | revision | A   | A        |                                       |        |               |          |                            |                       |
| index       | sheet    | 1   | 2        |                                       |        |               |          |                            | 1 of 2                |

| PRODUCT<br>NUMBER | SIZE | DIM. "A"    | DIM. "B"   | DIM. "S"    | N° POSITION<br>MOLDED CLOSED |
|-------------------|------|-------------|------------|-------------|------------------------------|
| 93692-X40K        | 2X20 | 55.26/2.176 | 48.26/1.90 | 51.43/2.025 | 20                           |
| 93692-X44K        | 2X22 | 60.34/2.376 | 53.34/2.10 | 56.51/2.225 | NONE                         |

NOTES :

1. MATERIAL : BASE AND COVER : 30% GLASS FILLED POLYESTER  
FLAME RETARDANT PER UL 94 VO  
COLOUR : GREY  
STRAIN RELIEF : UNREINFORCED THERMOPLASTIC  
FLAME RETARDANT PER UL 94 VO  
COLOUR : GREY  
CONTACT : PHOSPHOR BRONZE
2. PLATING : 0.38  $\mu\text{m}$  / 15  $\mu\text{m}$  Au OVER 1.27  $\mu\text{m}$  / 50  $\mu\text{m}$  Ni  
IN CONTACT AREA REMAINDER OF PRODUCT  
(IDC PART) 1.27  $\mu\text{m}$  / 50  $\mu\text{m}$  Ni.
3. A DASH "C" AT THE END OF THE PART NUMBER TO INDICATE  
A PACKAGING IN TUBE WITH STOPPER INSTEAD OF LABEL

|            |                       |                       |                       |
|------------|-----------------------|-----------------------|-----------------------|
| 93692-1YYK | <input type="radio"/> |                       | <input type="radio"/> |
| 93692-0YYK | <input type="radio"/> | <input type="radio"/> |                       |

| PRODUCT<br>CODE X | WITH<br>DOUBLE KEYS | STANDARD      | WITHOUT |
|-------------------|---------------------|---------------|---------|
|                   |                     | STRAIN RELIEF |         |

[illegible]