



Klinger 49

**High performance multiservice packing
for both valves & pumping applications.
Klingerlock braided from Gore GFO®
filament yarns.**

K49 is only one of the Klinger TopLine range of compression packings.

This is an optimised range introduced to provide users with gland sealing products that meet today's demanding services, offering effective and trouble-free sealing during application. To achieve this goal we have selected the best materials and the best production methods. The result is the Klinger TopLine packing range.

Ongoing Test & Development in line with Klinger philosophy will ensure the continued improvement of all TopLine products.

- Klinger 49 packing is manufactured from PTFE filaments, which have been specially treated to incorporate a graphite based lubricant.

- The Klingerlock braiding process is used.

- PTFE is extremely resistant to a wide range of chemicals, K49 is therefore only affected by very strong oxidising media such as molten alkali metals. (please contact Klinger for further advice)

- It is the graphite infusion which allows the rapid dispersion of heat thus enabling the packing to operate in high speed dynamic applications where pure PTFE packings are not normally effective. It is equally effective in valve applications.

- Due to its wide service capabilities K49 TopLine packing offers the user a packing material with excellent sealing life and the option of reducing the variety of packings that must be held as stock.

- K49 is clean to handle and requires only minimal gland loading to effect a seal. It is WRAS approved for use in potable water applications.



aerospace
sector
certification
scheme

BS EN 9100:2003, ISO 9001:2008
Certificate no: FM 10571

Head Office
KLINGER Ltd
Wharfedale Road
Euroway Trading Estate
Bradford BD4 6SG

Tel: 01274 688 222
Fax: 01274 688 549

TopLine Packing 49

Service Capabilities

When used in equipment in good mechanical condition and installed using our product guidelines the undernoted values apply:

- Minimum operating Temperature **-240°C**
- Maximum operating temperature **280°C**
- Maximum steam temperature **280°C**
- pH **0-14**
- Maximum static pressure **250 bar**
- Maximum dynamic pressure **20 bar**
- Maximum recip. pressure **200 bar**
- Maximum running speed **18 m/s**

Note: The packing should not be subjected to the maximums of temperature, pressure and speed simultaneously, for further advice please contact our technical department.

Forms of Supply

Klinger packings are offered in a range of standardised packages:

Size:
3mm to 25mm

Length:
8 metres per box

by weight:
sizes under 9.5mm 1kg/box
9.5mm to 12.5mm 2kg/box
sizes over 12.5mm 4kg/box

Alternative lengths and weights can be offered upon request, please contact Klinger for further details.

Klinger 49 is suitable for use as a general valve and pump packing within many industries, for example;

- Water Industry
- Distilleries
- Pulp & Paper Mills
- Breweries
- Petrochemical Plants
- Chemical Processing
- Refineries

K49 has WRAS approval for use with potable water.

Technical Advice

If you require additional technical information or would like Klinger to advise you on a particular application, then contact our Technical Department at the address shown.

It is advantageous to provide the following details:

1. Type of valve or pump
2. Working and test pressure
3. Temperature - steady or cycling
4. Rate of pressure & temperature increase
5. Medium and concentration
6. Operating speed
7. Special requirements
8. Details of stuffing box design