

JST

Hand crimping tool

Type: WC-590

Features

Parallel action
operation

Ratchet release

Easy readjustment
of load

Contact locator with
insulation-stop

Precisely ground
profiles

Ergonomic soft grips
colour: green

Fully recyclable

Applicable terminal:
() VM/F-61T-2.0

Cross section range:

Profile 1: 0.5mm²

Profile 2: 1.0mm²


Profile 3: 2.0mm²

Crimp height specification

0.5mm² – 1.10mm


1.0mm² – 1.35mm

2.0mm² – 1.60mm



Operating instructions see overleaf

OPERATION INSTRUCTIONS



1. Open flap locator and insert contact up to stop.
2. Close flap locator.
3. Close handtool until first ratchet.
4. Insert wire.
5. Close handtool until the ratchet releases.
6. Open flap locator and carefully remove the wire.

