






Rev	AWO #	Description	Date	Appr
-		RELEASED	7/31/09	

APPROVED: _____
DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:
Insulator: Thermoplastic, rated UL 94V-0
Insulator color: Black
Contacts: Brass
Plating:
Tin over Copper underplate
Electical:
Operating voltage: 250 VAC max
Current rating: 15 Amps max
Insulation resistance: 100 Mohms min @ 500 VDC
Dielectric withstanding voltage: 2000 VAC for 1 minute
Temperature Rating:
Operating temperature: -65°C to +125°C
Environmental:
Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

IEC CONNECTOR, ISOLATED FUSE
1.0mm SNAP IN, .187" [4.8] QC TERMINAL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM [INCHES] TOLERANCES, EXCEPT AS NOTED INCHES 10 X ± .10 .XX ± .020 .XXX ± .015 XXX ± .015			HOLE ØX ± .10 ØXX ± .015 ØXXX ± .010		DATE	
DRAWN	SS	7/31/09				
CHECKED						
APPROVED						
TITLE			SIZE	PART NO.	SCALE	REV.
X			X	IEC-GS-1-100	NTS	-
REF:			REF:	SCALE: NTS	SHEET 1 OF 1	