

BATTERY OPERATED ULTRA COMPACT MICRO LINE THERMAL PRINTERS



Part Number	Description	FTP-628MCLX5X	FTP-628MCL1XX	FTP-628MCL401
Type	auto loading	with or without cutter	without cutter	with cutter
Dot Structure	dots/line	384	384	384
Horizontal Dot Pitch	dots/mm (dpi)	8 (203)	8 (203)	8 (203)
Characters / line	digits	32	32	32
Font	H x W	12 x 24	12 x 24	12 x 24
Effective Width	mm	48	48	48
Printing Speed (maximum)	dot lines/sec	480	480	480
	mm/sec	60	60	60
Dot Pitch	mm	0.125	0.125	0.125
Operate Voltage (V)	Head & motor	4.2-8.5	4.2-8.5	4.2-8.5
	Logic	5	5	5
Dimensions (mm)	Standard	70W x 34D x 15.5H	70.3W x 33D x 15.5H	81W x 42D x 22H
	Interface boards	52L x 69W x 15H		70W x 60D x 12H
Weight (g)	Mechanism	053/054: 47	101/103: 46	
	Mech/cutter	353/354: 120		100
Life (wear)	100 M pulses	Mechanism	053/054: 50km	50km
	Cuts	Mech/cutter	353/354: 500K	500K
Paper width (mm)	Front feed	053, 353: 58		
	Rear feed	054, 354: 58		
	Easy Load Model		101/103: 58	58
	Cutter	Rotary		Guillotine
Remarks	Safety standard	UL recognized	UL recognized	UL recognized

Interface Board Part Numbers		Paper Insertion	Mechanism Part Numbers		
Centronics	FTP-628DCL300	Front/Rear	FTP-628MCL053/054		
		Easy Load Model		FTP-628MCL101/103	
Centronics mini	FTP-628DCL301	Front/Rear w/cutter	FTP-628MCL353/354		
Centronics mini	FTP-628DCL450	ELM w/cutter			FTP-628MCL401
Serial mini	FTP-628DSL305	Front/Rear	FTP-628MCL053/054		
		Easy Load Model		FTP-628MCL101/103	
Serial mini	FTP-628DSL306	Front/Rear w/cutter	FTP-628MCL353/354		
Serial mini	FTP-628DSL499	ELM w/cutter			FTP-628MCL401

OPTIONS:

Name	Cable length	Cable Part Numbers		
Interface cable (Centronics, DCL)	500 mm (19.7 inch)	FTP-628Y202	FTP-628Y202	FTP-628Y202
Interface cable (Serial, DSL)	500 mm (19.7 inch)	FTP-628Y302	FTP-628Y302	FTP-628Y302
Power supply cable	500 mm (19.7 inch)	FTP-628Y402	FTP-628Y402	FTP-628Y402

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Fujitsu:](#)

[FTP-628Y302](#)