




L → C → R: 300±100gf
L → C → R: 300±100gf




(8) 0.9^{+0.1}_{-0.0} DIA

(4) 1.2^{+0.1}_{-0.0} DIA



RECOMMEND P.C.B. HOLES



CIRCUIT: DP3T

CONTACT CONFIGURATION

SWITCH FUNCTION		
PDS. 1	PDS. 2	PDS. 3
3-1	3-2	3-4
7-5	7-6	7-8

NOTES:

1. ALL DIMENSIONS IN MM [IN]
2. TERM. NOS. FOR REF ONLY
3. RATING: DC 30V, 0.2A
4. TRAVEL: 2.0mm TYP.
5. INITIAL CONTACT RESISTANCE: 20 milliohms typ.
6. LIFE CYCLE @FULL LOAD: 10,000 Cycles Typ.
7. TIMING: NON-SPECIFIED
8. DVI: 500VAC Terminal To Ground.
9. 2002/95/EC (ROHS) COMPLIANT



D	REVISED & REDRAWN	1/15/09	BLR
C	REVISED & REDRAWN		
REV.	DESCRIPTION	DATE	CHKD

TOLERANCES	
0.0	±0.4
0.00	±0.25

TITLE		SCALE		DATE		DR		DWG		REV	
EG 2301A DP3T-Non-Specified		2:1		5/11/94		BLR		P040181		D	

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED