




Dimensions are in millimeters

Shell size	Number of contacts	A ^{+0.76} ₀	B ^{+0.25} ₀	C ^{±0.12}	F ^{+0.51} ₀	G ^{+0.25} ₀	H ^{+0.51} ₀	L ^{+0.22} ₀	Part Number
E	09	30.43	16.46	24.99	10.64	6.05	19.02	0.80	DE09S56*T
A	15	38.76	24.54	33.32	10.64	6.05	27.25	0.80	DA15S56*T
B	25	52.65	38.25	47.04	10.64	6.05	41.02	0.80	DB25S56*T
C	37	68.94	54.71	63.50	10.64	6.05	57.45	0.80	DC37S56*T

Plating: 4 --> Flash AU
Plating: 5 --> 0.75µ AU

DETAIL A: termination end

NOTES

Materiel and finish:

Housings:

Shells: steel, bright tin plated


Insulators: glass filled thermoplastic UL94V0

Contacts:

phosphor bronze, gold plated over nickel
on mating end, bright tin plated over nickel
on termination end

Brackets: glass filled thermoplastic UL94V0

Rivets: brass, bright tin plated



c	12/08/04	update P/N	--
ISS	DATE	Lastest modification by : M PESSON	MOD N°
Designed by: PESSON		date: 09/06/89	Type of drawing: CLIENT
Checked by : --		date: --	Released by: -- --
TITLE : SOCKET CONNECTORS D SUB. RIGHT ANGLED SPILL WITH PLASTIC BRACKETS			
SCALE	Special mfg: __	MATERIAL: __	N°: __
1.5	item list n°: --	--	--
	General Linear Tolerances: __	General machining --  surface texture: 	Geometrical Tolerances see NF E 04-552
			SHEET 1/1
		FRAMATOME CONNECTORS FRANCE Rue Louis Breguet - BP 05 72024 LE MANS Cedex Tel. 33 (16) 43.84.08.43	This document is the property of FRAMATOME CONNECTORS FRANCE It must not be reproduced or communicated without permission in writing flow the owners
FORMAT	SOURIAU DRG N°		PROJECT
A3	C01-8636-0517		D89D018