

REV	C	SRK-BS-MD-90-***
-----	---	------------------

REVISIONS			
SYM	DESCRIPTION	DATE	APPROVED
B	NEW RELEASE PER E.O. P20387	12-1-09	R.D.R.
C	REVISED PER E.O. P20577	8/16/10	DM

SRK - BS - MD - 90 - 001

SERIES PREFIX

BACKSHELL BS





SIZE MD MEDIUM

VERSION OF CORRUGATED CONDUIT
001 NW17 & NW22
002 NW22

90 BACKSHELL 90°

CONVOLUTE REQUIREMENTS:

RATED 125°C
NW17
OUTER Ø=21.20 [.835]
INNER Ø=16.60 [.654]
PITCH=2.30 [.091]
NW22
OUTER Ø=25.40 [1.000]
INNER Ø=21.30 [.839]
PITCH=3.10 [.122]



4. MATERIAL: PLASTIC; COLOR: BLACK.
3. THIS PART SNAPS ONTO SRK02-MD*-*** AND SRK06-MD*-***. *** = KEYS; *** = SEE 37322C-00013-01 FOR ARRANGEMENTS.
2. DIMENSIONAL TOLERANCE: ±.64 [.025].
1. ALL DIMENSIONS ARE IN MILLIMETERS [INCHES].

NOTES: UNLESS OTHERWISE SPECIFIED

SIGNATURE & DATE	
DR	JAMIE APOSTOL 06AUG2010
CHK	Paul M. Co 8/16/10
PE	Paul M. Co 8/16/10
APPD	DM 8/16/10
SCALE	NONE
WT	18.20 g

BACKSHELL 90° MEDIUM SIZE (MD) SRK SERIES	
ENVELOPE	

EP 201	MATL CODE 89
DEUTSCH INDUSTRIAL 3850 INDUSTRIAL AVE. HEMET, CA 92545	
C	SRK-BS-MD-90-***
DWG SIZE	CODE 11139 SHEET 1 OF 1