



Dimensions: mm (In.)

Type	Wire	Rating	Wire Color
441-R359A	12AWG	30A 12-24 VDC	Red
441-R359B	14AWG	20A 12-24 VDC	Red
441-R359C	16AWG	15A 12-24 VDC	Red
441-R359D	18AWG	10A 12-24 VDC	Red

SPECIFICATIONS	
Rating:	12 - 24 VDC
Contact Resistance	50m Ω max.
Insulation Resistance:	500VDC 100M Ω min.
Dielectric Strength:	1000VAC, 1 minute
Terminals:	Brass Tin (Sn) Plated
Body:	PVC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eagle Plastic Devices:

[441-R359B](#) [441-R359A](#) [441-R359C](#) [441-R359D](#)