





DATE	DESCRIPTION	REV.
12.22.09	CHANGE AS PER ECN 09-193	A
6.01.11	CHANGE AS PER ECN 11-078	B



Notes:

Material:

Shell: Steel, Nickel Plate.

Insulator: PBT, UL 94-V0

Contacts: Phosphor Bronze

Finish:

Contact Area: Gold Plate over Nickel Plate

on Solder Tail: Tin Plate over Nickel Plate

Electrical Specifications


Rated Voltage: 30V AC (rms)

Contact Current Rating: 1 A max.

Contact Resistance: 30 milliohms Max.

Dielectric Withstanding: 500V AC

Operating Temperature: -20°C to 85°C



KEYSTONE ELECTRONICS CORP.			
www.keystec.com • ASTORIA, N.Y. 11105-2017 • Tel (718) 956-8900			
PART NAME			
USB A-TYPE HORIZONTAL PC PLUG			
MATERIAL			
AS NOTED			
FINISH		DRN BY	DATE
AS NOTED		BOONE	6.13.06
TOLERANCES		APPD	SCALE
DECIMAL ± .010 [± 0.25]		LN	3X
ANGULAR ± 1°			
UNLESS OTHERWISE SPECIFIED		CODE	DWG NO.
		C/M	932

THIS DOCUMENT IS THE PROPERTY OF
KEYSTONE ELECTRONICS CORP. AND
SHALL NOT BE REPRODUCED, DISTRIBUTED
OR USED AS A BASIS FOR MANUFACTURE
WITHOUT PRIOR WRITTEN PERMISSION
FROM KEYSTONE ELECTRONICS CORP.