


Number of contacts

4-64



Pcb transition connector, 2 rows, low-profile with 5.5 mm height

Identification      No. of contacts      Part No.      Drawing      Dimensions in mm

Pcb transition connector<sup>2)</sup>

2 rows  
Standard low-profile version


|    |                |
|----|----------------|
| 4  | 09 18 104 9622 |
| 6  | 09 18 106 9622 |
| 8  | 09 18 108 9622 |
| 10 | 09 18 110 9622 |
| 14 | 09 18 114 9622 |
| 16 | 09 18 116 9622 |
| 20 | 09 18 120 9622 |
| 24 | 09 18 124 9622 |
| 26 | 09 18 126 9622 |
| 30 | 09 18 130 9622 |
| 34 | 09 18 134 9622 |
| 40 | 09 18 140 9622 |
| 50 | 09 18 150 9622 |
| 60 | 09 18 160 9622 |
| 64 | 09 18 164 9622 |

| No. of contacts | A $\pm 0.38$ | B $\pm 0.10$      |
|-----------------|--------------|-------------------|
| 4               | 10.38        | 2.54 x 1 = 2.54   |
| 6               | 12.92        | 2.54 x 2 = 5.08   |
| 8               | 15.46        | 2.54 x 3 = 7.62   |
| 10              | 18.00        | 2.54 x 4 = 10.16  |
| 14              | 23.08        | 2.54 x 6 = 15.24  |
| 16              | 25.62        | 2.54 x 7 = 17.78  |
| 20              | 30.74        | 2.54 x 9 = 22.86  |
| 24              | 35.78        | 2.54 x 11 = 27.94 |
| 26              | 38.32        | 2.54 x 12 = 30.48 |
| 30              | 43.40        | 2.54 x 14 = 35.56 |
| 34              | 48.48        | 2.54 x 16 = 40.64 |
| 40              | 56.10        | 2.54 x 19 = 48.26 |
| 50              | 68.80        | 2.54 x 24 = 60.96 |
| 60              | 81.50        | 2.54 x 29 = 73.66 |
| 64              | 86.58        | 2.54 x 31 = 78.74 |


Pcb transition connector<sup>2)</sup>

2 rows  
Kinked low-profile version  
2 kinked pins at each extremity

|    |                |
|----|----------------|
| 4  | 09 18 104 9422 |
| 6  | 09 18 106 9422 |
| 8  | 09 18 108 9422 |
| 10 | 09 18 110 9422 |
| 14 | 09 18 114 9422 |
| 16 | 09 18 116 9422 |
| 20 | 09 18 120 9422 |
| 24 | 09 18 124 9422 |
| 26 | 09 18 126 9422 |
| 30 | 09 18 130 9422 |
| 34 | 09 18 134 9422 |
| 40 | 09 18 140 9422 |
| 50 | 09 18 150 9422 |
| 60 | 09 18 160 9422 |
| 64 | 09 18 164 9422 |



Board drillings



<sup>1)</sup> Pitch tolerance:  $\pm 0.05$

<sup>2)</sup> Not released for halogen free flat cables