

NOTES: UNLESS OTHERWISE SPECIFIED

1. P/N: XELCOLOR
HOUSING & PLUNGER & SLIDE: MOLDED NYLON 6,6.
AVAILABLE IN TEN COLORS.


CONTACT NEEDLE: STAINLESS STEEL.
BANANA SOCKER: 360 1/2 HD. BRASS.
COMPRESSION SPRING: STAINLESS STEEL.

2. P/N: 9274COLOR
INSULATOR: MOLDED PVC. AVAILABLE IN TEN COLORS.
ALLIGATOR: STEEL. NICKEL PLATED.

3. P/N: W-600/COLOR
18AWG 65X36 TINNED COPPER
0.144 [3.66] O.D. PVC INSULATION
AVAILABLE IN TEN COLORS.

4. PERFORMANCE
MAXIMUM CURRENT: 4.0 AMPS
MAXIMUM VOLTAGE: 5000 W.V.D.C.
MAXIMUM TEMPERATURE: 221°F (105°C)

REVISIONS		DESCRIPTION	DATE	APPROVED
LTR				



		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ±	
--	--	---	--