


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [502598-3393](#)
Status: **Active**
Overview: [FFC-FPC \(SMT\)](#)
Description: 0.30mm Pitch Easy-On™ BackFlip™ Type FPC Connector, Right Angle, Surface Mount, Dual Contact Style, 1.15mm Mated Height, 33 Circuits



Series

image - Reference only

Documents:

[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-502598-002 \(PDF\)](#)
[Packaging Specification SPK-502598-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family FFC/FPC Connectors
Series [502598](#)
Overview [FFC-FPC \(SMT\)](#)
Product Name Easy-On™
UPC 887191146423

Physical

Circuits (Loaded) 33
Color - Resin Black, White
Contact Position Dual
Durability (mating cycles max) 10
Entry Angle 90° Angle
Mated Height 1.15mm
Material - Metal Copper Alloy, Phosphor Bronze
Material - Plating Mating Gold
Material - Plating Termination Gold, Tin
Net Weight 85.310/mg
Number of Rows 1
Orientation Right Angle
PCB Locator No
PCB Retention Yes
Packaging Type Embossed Tape on Reel
Pitch - Mating Interface 0.30mm
Polarized to PCB Yes
Stackable No
Temperature Range - Operating -40°C to +85°C
Termination Interface: Style Surface Mount
Wire/Cable Type FPC only

Electrical

Current - Maximum per Contact 0.2A
Voltage - Maximum 50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

[Packaging Specification](#) SPK-502598-001
[Product Specification](#) PS-502598-002, RPS-502598-012, RPS-502598-015
[Sales Drawing](#) SD-502598-003, SD-502598-004

EU RoHS

**ELV and RoHS
Compliant**
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[502598Series](#)

Mates With

[15015 0.30mm Premo-Flex™ Etched
Copper Polyimide Jumper](#)