


Model 109
5 mm Flush Face, Screw Mount LED




LED lamp mounts flush with panel face. **Mounting Hole Dia.:** 0.197" (5 mm). Nickel plated brass body with Lexan lens. 6" wire leads with 0.250" strip length. Available in the new ultra bright white as well as red, green, yellow, amber, ultra bright blue and ultra bright green.

Stock No.*	Mfr.'s Type*	Voltage	EACH		
			1-99	100-499	500-999
265-109X	109-2X	2 VDC†	9.36	8.59	7.85
265-109X	109-5X	5 VDC	9.36	8.59	7.85
265-107X	109-12X	12 VDC	9.36	8.59	7.85
265-105X	109-24X	24 VDC	9.36	8.59	7.85
265-106X	109-28X	28 VDC	9.36	8.59	7.85
265-108Y	109-5Y	5 VDC	11.33	10.39	9.49
265-107Y	109-12Y	12 VDC	11.33	10.39	9.49
265-105Y	109-24Y	24 VDC	11.33	10.29	9.49
265-106Y	109-28Y	28 VDC	11.33	10.39	9.49

*Specify LED color, insert 1-red, 2-green, 3-yellow, 4-amber where X appears. Insert 5-ultra bright green, 6-ultra bright blue or 7-ultra bright white where Y appears. †External resistor required.

Model 500I and 5002 1/2" Snap Mount



Model 500I 1/2" Snap Mount Incandescent

Snap mount incandescent light. **Mounting Hole Dia.:** 0.500" (12.7 mm). High brightness incandescent lamp. Rugged nylon body, Lexan lens. Available in 0.187" O.C. terminals or 6" leads.

0.187" QC Termination

Stock No.*	Mfr.'s Type*	Voltage	EACH		
			1-99	100-499	500-999
265-301X	500I-5XQC	5 VDC	2.26	2.03	1.87
265-302X	500I-12XQC	12 VDC	2.26	2.03	1.87
265-303X	500I-24XQC	24 VDC	2.26	2.03	1.87
265-311X	500I-28XQC	28 VDC	2.26	2.03	1.87

6" Lead Termination

265-304X	500I-56X	5 VDC	1.62	1.42	1.31
265-305X	500I-126X	12 VDC	1.62	1.42	1.31
265-306X	500I-246X	24 VDC	1.62	1.42	1.31
265-321X	500I-286X	28 VDC	1.50	1.38	1.32

*Specify lens color, insert 1-red, 2-green, 3-yellow, 4-amber, 5-blue, 6-clear where X appears.

Model 5002 1/2" Snap Mount LED

Snap mount LED light. **Mounting Hole Dia.:** 0.500" (12.7 mm). Rugged nylon body, Lexan lens. Large 10 mm LED. Available in 0.250" O.C. terminals or 6" leads.

0.250" QC Termination


265-307X	5002-5XQC	5 VDC	1.85	1.67	1.53
265-308X	5002-12XQC	12 VDC	1.85	1.67	1.53
265-309X	5002-24XQC	24 VDC	1.85	1.67	1.53
265-331X	5002-28XQC	28 VDC	1.87	1.72	1.65
265-317Y	5002-5YQC	5 VDC	3.50	3.23	3.09
265-327Y	5002-12YQC	12 VDC	3.50	3.23	3.09
265-347Y	5002-24YQC	24 VDC	3.50	3.23	3.09
265-332Y	5002-28YQC	28 VDC	3.50	3.23	3.09

6" Lead Termination

265-401X	5002-56X	5 VDC	1.78	1.57	1.44
265-402X	5002-126X	12 VDC	1.78	1.57	1.44
265-403X	5002-246X	24 VDC	1.78	1.57	1.44
265-341X	5002-286X	28 VDC	1.78	1.57	1.44
265-455Y	5002-56Y	5 VDC	2.98	2.75	2.63
265-422Y	5002-126Y	12 VDC	2.98	2.75	2.63
265-442Y	5002-246Y	24 VDC	2.98	2.75	2.63
265-452Y	5002-286Y	28 VDC	2.98	2.75	2.63

*Specify LED color, insert 1-red, 2-green, 3-yellow, 4-amber where X appears. Insert 5-ultra bright green, 6-ultra bright blue or 7-pure white where Y appears. †External resistor required.

Model 150
5/32" Snap Mount LED




Panel mount LED light. **Mounting Hole Dia.:** 0.156" (4.68 mm). Rugged, black nylon body. 6" leads with 0.250" strip length. Available in red, green, yellow, amber, ultra bright blue and pure white.

Stock No.*	Mfr.'s Type*	Voltage	EACH		
			1-99	100-499	500-999
265-502X	150-2X	2 VDC†	1.18	1.03	.95
265-503X	150-5X	5 VDC	1.36	1.19	1.09
265-504X	150-12X	12 VDC	1.36	1.19	1.09
265-501X	150-24X	24 VDC	1.36	1.19	1.09
265-505X	150-28X	28 VDC	1.36	1.19	1.09
265-506Y	150-5Y	5 VDC	5.28	4.74	4.36
265-507Y	150-12Y	12 VDC	5.28	4.74	4.36
265-509Y	150-24Y	24 VDC	5.28	4.74	4.36
265-508Y	150-28Y	28 VDC	5.28	4.74	4.36

*Specify LED color, insert 1-red, 2-green, 3-yellow, 4-amber where X appears. Insert 5-ultra bright green, 6-ultra bright blue or 7-pure white where Y appears. †External resistor required.

T 1 LED Model 205 Panel Mount Fixed Lamp LED




Incorporates a T-1 size LED in an all metal threaded body. Lamp supplied with flat Lexan transparent lens the same color as the LED and 6" wire leads. **Mounting Hole Dia.:** 0.250" (6.35 mm).

Stock No.*	Mfr.'s Type*	Voltage	EACH		
			1-99	100-499	500-999
265-270X	205-2X	2 VDC†	6.12	5.61	5.18
265-271X	205-5X	5 VDC	6.32	5.80	5.35
265-272X	205-12X	12 VDC	6.32	5.80	5.35
265-273X	205-24X	24 VDC	6.32	5.80	5.35
265-274X	205-28X	28 VDC	6.32	5.80	5.35
265-275Y	205-5Y	5 VDC	9.63	8.82	8.14
265-276Y	205-12Y	12 VDC	9.63	8.82	8.14
265-277Y	205-24Y	24 VDC	9.63	8.82	8.14
265-278Y	205-28Y	28 VDC	9.63	8.82	8.14

*Specify LED color, insert 1-red, 2-green, 3-yellow, 4-amber where X appears. Insert 5-ultra bright green, 6-ultra bright blue or 7-pure white where Y appears. †External resistor required.

Model 252
5/16" Low Profile Screw Mount LED




Panel mount LED light. **Mounting Hole Dia.:** 0.156" (4.68 mm) black anodized aluminum body. 6" leads with 0.250" strip length. Available in red, green, yellow, amber, ultra bright green, ultra bright blue and pure white.

Stock No.	Mfr.'s Type	Voltage	EACH		
			1-99	100-499	500-999
265-601X	252-2X	2 VDC†	4.57	4.09	3.76
265-602X	252-5X	5 VDC	5.13	4.60	4.23
265-603X	252-12X	12 VDC	5.13	4.60	4.23
265-721X	252-24X	24 VDC	5.13	4.60	4.23
265-604X	252-28X	28 VDC	5.13	4.60	4.23
265-605Y	252-5Y	5 VDC	8.57	7.83	7.20
265-606Y	252-12Y	12 VDC	8.57	7.83	6.91
265-731Y	252-24Y	24 VDC	8.57	7.83	7.20
265-607Y	252-28Y	28 VDC	8.57	7.83	7.20

*Specify LED color, insert 1-red, 2-green, 3-yellow, 4-amber where X appears. Insert 5-ultra bright green, 6-ultra bright blue or 7-pure white where Y appears. †External resistor required.

Panel Mount Indicator Lights

Model 240
1/4" Snap Mount LED




Panel mount LED light. **Mounting Hole Dia.:** 0.250" (6.35 mm). Rugged, black nylon body. 6" leads with 0.250" strip length. Available in red, green, yellow, amber, ultra bright green, ultra bright blue and pure white.

Stock No.*	Mfr.'s Type*	Voltage	EACH		
			1-99	100-499	500-999
265-404X	240-2X	2 VDC†	1.18	1.03	.95
265-405X	240-5X	5 VDC	1.36	1.19	1.09
265-406X	240-12X	12 VDC	1.36	1.19	1.09
265-411X	240-24X	24 VDC	1.36	1.19	1.09
265-407X	240-28X	28 VDC	1.36	1.19	1.09
265-408Y	240-5Y	5 VDC	5.28	4.74	4.36
265-409Y	240-12Y	12 VDC	5.28	4.74	4.36
265-411Y	240-24Y	24 VDC	5.28	4.74	4.36
265-501Y	240-28Y	28 VDC	5.28	4.74	4.36

*Specify LED color, insert 1-red, 2-green, 3-yellow, 4-amber where X appears. Insert 5-ultra bright green, 6-ultra bright blue or 7-pure white where Y appears. †External resistor required.

T -13/4" LED Model 444 Front Flush Mount Indicator Water Resistant




Low profile design comes with a lens for a neat panel appearance and 6" wire leads. **Mounting Hole Dia.:** 0.312" (7.94 mm). O-ring supplied to seal between the panel and the indicator from dust and water.

Stock No.*	Mfr.'s Type*	Voltage	EACH		
			1-99	100-499	500-999
265-291X	444-2X	2 VDC†	8.63	7.97	7.62
265-292X	444-5X	5 VDC	8.68	8.02	7.66
265-293X	444-12X	12 VDC	8.68	8.02	7.66
265-294X	444-24X	24 VDC	8.68	8.02	7.66
265-295X	444-28X	28 VDC	8.68	8.02	7.66
265-296Y	444-5Y	5 VDC	11.82	10.91	10.43
265-297Y	444-12Y	12 VDC	11.82	10.91	10.43
265-298Y	444-24Y	24 VDC	11.82	10.91	10.43
265-299Y	444-28Y	28 VDC	11.82	10.91	10.43

*Specify LED color, insert 1-red, 2-green, 4-amber where X appears. Insert 5-ultra bright green, 6-ultra bright blue or 7-pure white where Y appears. †External resistor required.

T-1 LED Model 621 Panel Front Mount



Reflector engineered to allow maximum light distribution. **Mounting Hole Dia.:** 0.236" (6 mm). For panel thickness up to 0.156" (3.97 mm). Metal thread body with 6" wire leads.

Stock No.*	Mfr.'s Type*	Voltage	EACH		
			1-99	100-499	500-999
265-279X	621-2X	2 VDC†	2.43	2.23	2.06
265-280X	621-5X	5 VDC	2.84	2.60	2.40
265-281X	621-12X	12 VDC	2.84	2.60	2.40
265-283X	621-24X	24 VDC	2.84	2.60	2.40
265-284X	621-28X	28 VDC	2.84	2.60	2.40
265-285Y	621-5Y	5 VDC	5.15	4.75	4.54
265-286Y	621-12Y	12 VDC	5.15	4.75	4.54
265-287Y	621-24Y	24 VDC	5.15	4.75	4.54
265-288Y	621-28Y	28 VDC	5.15	4.75	4.54

*Specify LED color, insert 1-red, 2-green, 3-yellow, 4-amber where X appears. Insert 5-ultra bright green, 6-ultra bright blue or 7-pure white where Y appears. †External resistor required.