


95

95 Cable Cutters, Ratchet Action

patented



95 31 250



95 36 250



95 31 280



- ▶ for cutting copper and aluminium cables, single and multiple wire
- ▶ **not suitable for steel wire and wire ropes**
- ▶ precision ground, hardened blades
- ▶ clean and smooth cut without crushing and deformation
- ▶ one-hand operation using ratchet principle
- ▶ little handforce required due to optimum transmission ratio
- ▶ two-stage ratchet drive for easy cutting
- ▶ simple handling as a result of low weight and compact design – can be used even in confined areas
- ▶ with guard
- ▶ special grade tool steel

Models 95 31 250/280:

- ▶ fixed handle with support area for putting down the plier when cutting

Models 95 31/36 280:


- ▶ suitable for aluminium sector cable up to 4 x 150 mm²

special

Cutting thicker cables usually requires a high handforce. KNIPEX Ratchet Cable Cutters facilitate this work by means of a two-stage ratchet drive and a handle with support (model 95 31). The cable cutter can be rested on a solid ground so that additional body weight can be applied to lower arm musculature fatigue.



Article-No.	EAN-Code	Head	Handles	Cutting capacity			
Length mm	4003773-			⌀ mm	mm ²	MCM	g
95 31 250	043935	lacquered	with two-colour	32	240	500	575
280	043942		dual component handles	52	380	750	750
95 36 250	026884	lacquered	insulated with two-colour	32	240	500	560
280	026891		dual component handles	52	380	750	735
			⚠ 1000 V ⚡ VDE-tested				
95 39 250	022244	spare moving blade					130
95 39 280	025283	spare moving blade					260



95 31 280: large cutting capacity: maximum 52 mm dia. / 380 mm²



Ratchet principle and two-stage ratchet drive for easier cutting.