

Regina reflector for Osram Oslon SSL/SX LEDs



- Designed & optimized for Osram Oslon series of LEDs
- Reflector material metallized PC. with high UV and temperature resistance (120°C/248°F). Allows use of high current and temperature conditions
- Best available optical efficiency, over 90%
- Small position pins, fastening to heat sink with droplets of glue.
- Please check fastening details from this link:
(http://www.ledil.com/datasheets/DataSheet_GLUES.pdf)
- Compact dimensions 19mm x 15.3 mm (+ position pins 2.5mm)


REFLECTOR TYPES

NAME	ORDERING CODE	FWHM Angle
Regina reflector	C11347_Regina-OSL	±5°

NAME	ORDERING CODE	FWHM Angle
Regina reflector	C11347_Regina-OSL-SX	To be measured shortly


MEASUREMENTS

Relative Intensity of C11347_Regina-OSL



© Ledil Oy – PRELIMINARY - Subject to change without prior notice

DRAWINGS



© Ledil Oy – PRELIMINARY - Subject to change without prior notice