




Material : Thermoplastic with glass fiber
Classified UL 94 V0 Black

Spécification : Temperature range -40°C to 150°C

XX : Number of points : 02 to 18

This document and drawings, sketches, and schematic drawings are the property of the NICOMATIC company, and no parts thereof may be reproduced and used without the written consent of the owner. Law dated 11.03.1902

 www.nicomatic.com Mail : nicomatic@nicomatic.fr Tel : +33 (0)4.50.36.13.85	2	04/05/09	H.L.	E.M.	D.Z.
	Iss	Date	Drawn	Checked	Approved
Item : Female housing for crimping contact, pitch=2.54mm					
Folder : X:\Méthodes\Plans clients\Plans clients 2D\31 - Connecteurs et dérivés HE13-HE14\01-Boîtiers\Fil discret\2SXX_cl					
			General tolerance	±0.2	Scale 5:1
					Page 1/1

Catalogue Reference : 2SXX