

A.  
System  
Overview

B1.  
Cable Ties

B2.  
Cable  
Accessories

B3.  
Stainless  
Steel Ties

C1.  
Wiring  
Duct

C2.  
Surface  
Raceway

C3.  
Abrasion  
Protection

C4.  
Cable  
Management

D1.  
Terminals

D2.  
Power  
Connectors

D3.  
Grounding  
Connectors

E1.  
Labeling  
Systems

E2.  
Labels

E3.  
Pre-Printed  
& Write-On  
Markers

E4.  
Permanent  
Identification


E5.  
Lockout/  
Tagout  
& Safety  
Solutions

F.  
Index




## Pan-Ty® Ladder Style Releasable Wing Push Mount Ties – Heat Stabilized Nylon 6.6

- For high temperature applications up to 239°F (115°C) – indoor use
- Unique releasable ladder design eliminates the need for multiple clamp sizes
- Cable tie, mount, and fastener in a single part



- Used to attach bundles to another surface such as a flat panel
- Anchor is easily pressed into a pre-formed hole and locks in place
- Wings provide constant tension for a stable, secure, and rattle-free installation
- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation



| Part Number | Length |    | Width |    | Thickness |    | Nominal Hole Dia. |    | Max. Panel Thickness |    | Max. Bundle Dia. |    | Min. Loop Tensile Str. |   | Recommended Installation Tool | Std. Pkg. Qty. | Std. Ctn. Qty. |
|-------------|--------|----|-------|----|-----------|----|-------------------|----|----------------------|----|------------------|----|------------------------|---|-------------------------------|----------------|----------------|
|             | In.    | mm | In.   | mm | In.       | mm | In.               | mm | In.                  | mm | In.              | mm | Lbs.                   | N |                               |                |                |

### Standard Cross Section



|                     |     |     |      |     |      |     |      |     |      |     |      |    |    |     |                   |     |      |
|---------------------|-----|-----|------|-----|------|-----|------|-----|------|-----|------|----|----|-----|-------------------|-----|------|
| <b>PRLWP30S-D30</b> | 4.7 | 119 | .380 | 9.7 | .050 | 1.3 | .266 | 6.8 | .118 | 3.0 | 1.43 | 36 | 35 | 156 | Hand install only | 500 | 5000 |
| <b>PRLWP50S-D30</b> | 7.1 | 180 | .380 | 9.7 | .050 | 1.3 | .266 | 6.8 | .118 | 3.0 | 2.18 | 55 | 35 | 156 |                   | 500 | 5000 |

## Pan-Ty® Umbrella Wing Push Mount Ties – Nylon and Heat Stabilized Nylon 6.6

- Natural nylon material for indoor use
- Heat stabilized material for high temperature applications up to 239°F (115°C) – indoor use
- Quick, secure way to fasten to clearance holes in panel
- Anchor is easily pressed into a pre-formed hole in a light gauge metal or plastic and locks in place



- Umbrella shaped disk provides constant tension for a stable, secure, and rattle-free installation
- Disk forms a dust-tight and semi-liquid tight seal to the panel surface
- PLUP40SE style is for use with corrugated loom tubing, see page C3.11
- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation



| Part Number | Length |    | Width |    | Thickness |    | Nominal Hole Dia. |    | Max. Panel Thickness |    | Max. Bundle Dia. |    | Min. Loop Tensile Str. |   | Recommended Installation Tool | Std. Pkg. Qty. | Std. Ctn. Qty. |
|-------------|--------|----|-------|----|-----------|----|-------------------|----|----------------------|----|------------------|----|------------------------|---|-------------------------------|----------------|----------------|
|             | In.    | mm | In.   | mm | In.       | mm | In.               | mm | In.                  | mm | In.              | mm | Lbs.                   | N |                               |                |                |

### Standard Cross Section

|                      |     |     |      |     |      |     |      |     |      |     |      |    |    |     |                                                        |     |      |
|----------------------|-----|-----|------|-----|------|-----|------|-----|------|-----|------|----|----|-----|--------------------------------------------------------|-----|------|
| <b>PLUP40S-D30*</b>  | 7.0 | 177 | .190 | 4.8 | .047 | 1.2 | .266 | 6.8 | .050 | 1.3 | 1.57 | 40 | 50 | 222 | GTS, GTSL, GS2B, GTH, GS4H, PTS, PTH, PPTS, STS2, STH2 | 500 | 5000 |
| <b>PLUP40SE-D</b>    | 7.0 | 177 | .190 | 4.8 | .047 | 1.2 | .266 | 6.8 | .050 | 1.3 | 1.57 | 40 | 50 | 222 |                                                        | 500 | 5000 |
| <b>PLUP40SE-D30*</b> | 7.0 | 177 | .190 | 4.8 | .047 | 1.2 | .266 | 6.8 | .050 | 1.3 | 1.57 | 40 | 50 | 222 |                                                        | 500 | 5000 |

\*Heat stabilized material (30).