




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

Material	High Conductivity Seamless Copper Tube
Plating	Electro-Tin
Wire Size	3/0 AWG
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric
Wire Strip Length	7/8 in.
Stud Size	3/8 in.
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.
UL Temperature Rating	90° C
C.S.A Certified Wire Connector	Yes
Panduit Color Code on Barrel	ORANGE
Panduit Die Index No. on Barrel	P50
Alternate Industry Die Index No. () on Barrel	(14)



								TINLEY PARK, ILLINOIS	
						LCAS3/0-38F-X		Copper Lug - One-Hole, Short Barrel, 90° Angle Tongue	
00	9/02	SAB	DRL	RELEASED		10326			
REV	DATE	BY	CHK	DESCRIPTION		ECN	SCALE	DRAWING NO / CAD FILE	
							N/A	LCAS3_0-38F-CUST	