



.050" FLEX CARD TERMINAL FCF SERIES


SPECIFICATIONS

Materials:
Insulator Material: Black Liquid Crystal Polymer
Terminal Material: Phosphor Bronze
Current Rating: 2A @ 80°C ambient
Operating Temp Range: -65°C to +105°C with Tin; -65°C to +125°C with Gold
Max Processing Temp: 230°C for 60 seconds
Plating: Sn or Au over 50µ" (1,27µm) Ni

Mates with: EMF



APPLICATIONS



Note: Some lengths, styles and options are non-standard, non-returnable.

FCF - 1 NO. PINS PER ROW - LEAD STYLE - PLATING OPTION - D - CARD SLOT - TAIL OPTION - SL

20, 30, 40 & 50
(Call Samtec for other sizes)


Specify LEAD STYLE from chart

-L = 10µ" (0,25µm) Gold on post 75µ" (1,90µm) Tin on tail

-S = 30µ" (0,76µm) Gold on post 75µ" (1,90µm) Tin on tail

-01 = Accepts (0,80mm) .031" thick card

-RA = Right Angle (Leave blank for vertical version. Style -02 only)



Due to technical progress, all designs, specifications and components are subject to change without notice.