

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [84729-0005](#)
Status: **Active**
Overview: [Industrial Products](#)
Description: USB Type A Panel Mount Receptacle-to-USB Type A Plug Cordset, 1.50m Length

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-84727-002 \(PDF\)](#)


General
Product Family Cable Assemblies
Series [84729](#)
Comments Fully shielded for EMI/RFI protection
Connector to Connector Type A Recept-to-Type A Plug
Overview [Industrial Products](#)
Product Name Industrial USB

Physical
Cable Length 1.50m
Circuits (Loaded) 4
Color - Resin Black
Gender Dual
Lock to Mating Part None
Material - Resin Nylon, Polyester
Packaging Type Bag
Pitch - Mating Interface 2.00mm, 2.50mm
Single Ended No
Waterproof / Dustproof Yes
Waterproof / Dustproof Type IP67, NEMA 6P
Wire Insulation Diameter 3.89mm (.15")
Wire Size AWG N/A
Wire/Cable Type USB

Electrical
Current - Maximum per Contact 1A
Impedance Non-constant
Shield Type Full Shield
Shielded Yes
Voltage - Maximum 30V AC (RMS)

Material Info
UPC 822348832514

Reference - Drawing Numbers
Product Specification PS-84727-002
Sales Drawing SD-84729-006



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[84729Series](#)

Mates With
[84727 USB Type A Plug to Shielded Pigtail Receptacles](#)