



Sockets Metric, Long, K7806M

Long sockets in metric sizes.

Drive: 1/2" DIN 3121-G 12,5, ISO 1174.


Finish: cold forged, phosphated.

Material: CHROMO-EXTRA

Reinforced design, especially suited for wheel nuts.

T = depth of female hexagon.

With Dynamic-Drive-Profile



				L mm	D1 mm	D2 T mm mm		
K7806M-10		1844677	1	10	80	17.5	25 7.6 K560F-4 215	
K7806M-11		1844684	1	11	80	18.0	25 8.6 K560F-4 215	
K7806M-12		1844691	1	12	80	19.3	25 9.4 K560F-4 215	
K7806M-13		1805944	1	13	80	20.9	25 10.2 K560F-4 220	
K7806M-14		1844707	1	14	80	22.3	25 10.7 K560F-4 220	
K7806M-16		1844714	1	16	80	24.4	30 12.0 K560F-5 320	
K7806M-17		1805951	1	17	80	25.2	30 12.7 K560F-5 320	
K7806M-18		1844721	1	18	80	26.8	30 12.7 K560F-5 320	
K7806M-19		1805968	1	19	80	28.5	30 14.0 K560F-5 320	
K7806M-21		1823597	1	21	83	31.4	30 14.2 K560F-5 350	
K7806M-22		1805975	1	22	89	32.7	30 14.2 K560F-5 390	
K7806M-23		1844738	1	23	89	34.0	30 16.3 K560F-5 490	
K7806M-24		1805982	1	24	89	34.9	30 16.3 K560F-5 490	
K7806M-27		1805999	1	27	89	38.9	30 20.3 K560F-5 495	
K7806M-30		1844578	1	30	89	42.8	30 21.6 K560F-5 535	