

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300480040

Status:

Active

Overview:


Brad Industrial Ethernet Solutions

Description:

Micro-Change (M12) Single-Ended Cordset, 4 Poles, Male (Straight) to Pigtail, 24 AWG, PVC Cable, 4 Poles, 5.0m (16.40') Length

|                               |                                                      |
|-------------------------------|------------------------------------------------------|
| Documents:                    |                                                      |
| <a href="#">Drawing (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a> |

|                               |                                    |
|-------------------------------|------------------------------------|
| Agency Certification          |                                    |
| UL                            | E200650                            |
| General                       |                                    |
| Product Family                | Industrial Cordsets                |
| Series                        | 130048                             |
| Connector End A               | Micro-Change (M12)                 |
| Connector End B               | Pigtail                            |
| IP Rating                     | IP67                               |
| Material - Contact            | Copper Alloy                       |
| Overview                      | Brad Industrial Ethernet Solutions |
| Performance Category          | 5e                                 |
| Product Name                  | Micro-Change (M12)                 |
| Protocol                      | N/A                                |
| Region                        | America, Asia, Europe              |
| Type                          | Single Ended                       |
| UPC                           | 78678803900                        |
| Physical                      |                                    |
| Cable Diameter                | 5.59mm (.220")                     |
| Cable Length                  | 5.0m (16.40')                      |
| Color - Cable Jacket          | Teal                               |
| Coupling Style                | Threaded                           |
| Gender                        | Male-Pigtail                       |
| Keyway                        | D-coded                            |
| LED Indicator                 | No                                 |
| Material - Cable Jacket       | PVC                                |
| Material - Connector Body     | PVC                                |
| Material - Coupling Nut       | Nickel-plated Brass                |
| Material - Plating Mating     | Gold                               |
| Net Weight                    | 222.270/g                          |
| Orientation                   | Straight to Pigtail                |
| Poles                         | 4                                  |
| Temperature Range - Operating | -20°C to +75°C                     |
| Wire Size AWG                 | 24                                 |
| Wire/Cable Type               | N/A                                |
| Electrical                    |                                    |
| Current - Maximum per Contact | 1.5A                               |
| Voltage - Maximum             | 30V                                |
| Material Info                 |                                    |
| Engineering Number            | E10A00603M050                      |
| Reference - Drawing Numbers   |                                    |
| Sales Drawing                 | SD-120108-013                      |



|                                                               |               |
|---------------------------------------------------------------|---------------|
| EU ELV                                                        |               |
| Not Relevant                                                  |               |
| EU RoHS                                                       | China RoHS    |
| Not Reviewed                                                  |               |
| REACH SVHC                                                    |               |
| Not Contained Per - ED/108/2014 (17 Dec 2014)                 |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Not Low-Halogen                                               |               |
| For more information, please visit <a href="#">Contact US</a> |               |
| China ROHS                                                    | 50 Image      |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

|                             |
|-----------------------------|
| Search Parts in this Series |
| 130048 Series               |

This document was generated on 06/08/2020

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**