







PC card drilling dimensions(after plating) _____
(thickness 1.60±0.20mm)



Copyright FCI.

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	TIN LEAD	LEAD FREE
09	30.81	24.99	16.96	16.21	10.96	D09S24A.GL00	D09S24A.GL00LF
15	39.14	33.32	25.18	24.54	19.18	D15S24A.GL00	D15S24A.GL00LF
25	53.03	47.04	39.12	38.25	33.12	D25S24A.GL00	D25S24A.GL00LF
37	69.32	63.50	55.68	54.71	49.68	D37S24A.GL00	D37S24A.GL00LF

Plating: 4 --> flash AU
Plating: 6 --> 0.76µ AU

rev	ecn no	dr	date
B	-	CJA	1999/10/18
C	LS05-001	MPE	2005/01/11
D	LS05-0056	MPE	2005/06/28
E	LS06-0097	LGO	2006/07/28
F	LS08-0172	MPE	2008/08/13
G	I10-0059	NG	2010-02-23
-	-	-	-

www.fciconnect.com				surface	ISO 1302	tolerance std	ISO 406	ISO 1101	projection	mm	Scale
				ISO 1302	tolerance std	ISO 406	ISO 1101	projection	mm	Scale	
				tolerances unless otherwise specified	tolerances unless otherwise specified	tolerances unless otherwise specified	tolerances unless otherwise specified	tolerances unless otherwise specified	tolerances unless otherwise specified	tolerances unless otherwise specified	tolerances unless otherwise specified
Dr	JOURBERT	1999/10/18	ANGULAR	0.X	±0.1	size	A3	ECN	I10-0059	Rev.	
Eng	PESSON	1999/10/18	LINEAR	0.XX	±0.1	size	A3	ECN	I10-0059	Rev.	
Chr	NIRMAL GEORGE	2010-02-23	0.XX	±0.1	size	A3	ECN	I10-0059	Rev.		
Appr	SUDHIR VARMA	2010-02-23	Product family	D-SUB	Spec ref	-					
FCI				FEMALE CONNECTOR EUROPE				C01-8646-0494			
STRAIGHT STB FOR PCB 1.60mm				CUSTOMER				sheet 1 of 1			

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0000