

ELECTRONICS PLIERS

▼ SNIPE-NOSE PLIERS

431.LMT

▷ ISO 9655

- Slim joint for precision work.

ΔΔ: 80 g.



▼ MINI COMBINATION PLIERS


443.12 MT

- Side wire-cutter, capacity up to Ø1.7 mm in Cu, Ø 1 mm in mild steel.

- Stocky serrated nose, with tube-grip.

- Matt black anti-glare finish.

ΔΔ: 80 g.



◆◆ HALF-ROUND NOSE GRIPPING PLIERS



- These pliers serve all professional needs in laboratory, production and maintenance applications.
- Smooth, half-round jaws with contoured inside edges to protect components.
- Matt black non-reflective finish. Leaf spring.

▼ "TELEPHONE" PLIERS

442.MT

▷ ISO 9655

- Long stocky nose with fine end serrations.

- Side cutter.

- Cu wire max. Ø 2 mm.

- Fe wire 30 HRC max. Ø 1 mm.

ΔΔ: 88 g.

