

2.54*7.62mm (0.100"*0.300") DIP PLUG CONNECTOR




SPECIFICATIONS

Current Rating: 1.0 AMP
Voltage Rating: 500V AC/DC
Withstand Voltage: 1000V AC/DC
Contact Resistance: 20mΩ Max
Insulation Resistance: 1000MΩ Min
Operation Temperature: -40℃ to +105℃

Contact Material: Brass
Contact plating: Au or Sn Over 50U" Ni
Insulator Material: PBT+30%GF (UL94V-0)

ADIP-X-Z-LC

of Contacts
1 - 08, 10, 14, 16, 20



REVISION DATA			
ITEM	DESCRIPTION	DATE	REMARK
BA			
BA			

RoHS
compliant

N0. of contacts	Dim A	Dim B
08	07.62	15.42
10	10.16	17.96
14	15.24	23.04
16	17.78	25.58
18	20.32	28.12
20	22.86	30.66
24	27.94	35.74
26	30.48	38.28
28	33.02	40.82
32	38.10	45.90
34	40.64	48.44
36	43.18	50.98
40	48.26	56.06

ASSMANN
Electronics, Inc.

TOLERNCE		
X.	$\pm 5^\circ$	X.
. X	$\pm 2^\circ$	. X ± 0.38
. XX	$\pm 1^\circ$	. XX ± 0.25
. XXX	$\pm 0.5^\circ$	. XXX ± 0.12

DRAWN

CHECKED

APPROVE

PROJECT

UNIT

SCALE

EDITION

DATE



MM

3: 1

B0

04-11-22

PART NO

DRAW NO

NAME

ADIPXX-Z-LC-R

ASM5350-XXBXXX

2.54*7.62mm DIP plug connector

Issue No

PAGE

WF-

1/1