


DO NOT
SCALE FROM
THIS PRINT

TABLE 2	
LEAD STYLE	"A"
-01	.085 [2.16]
-03	.116 [2.95]







CLT-1XX-XX-XX-D

No OF POSITIONS
-02 THRU -50
(PER ROW)

LEAD STYLE
-01: THROUGH HOLE
(USE C-114-02-XX)
(SEE NOTE 7)
-03: THROUGH HOLE
(USED C-114-03-XX)


BODY SPECIFICATION
-D: DOUBLE ROW

PLATING SPECIFICATION
(VALUES GIVEN ARE IN MICRO-INCHES)
-G: GOLD, 10 Au / 50 Ni MIN ON CONTACT,
3 Au / 50 Ni MIN ON TAIL.
-S: SELECTIVE, 30 Au / 50 Ni MIN
ON CONTACT, MATTE TIN TAIL.
-F: FLASH SELECTIVE, 3 Au / 50 Ni MIN
ON CONTACT, MATTE TIN TAIL.
-SM: SELECTIVE, 30 Au / 50 Ni MIN
ON CONTACT, MATTE TIN TAIL.
-FM: FLASH SELECTIVE, 3 Au / 50 Ni MIN
ON CONTACT, MATTE TIN TAIL.
-L: LIGHT SELECTIVE, 10 Au / 50 Ni MIN
ON CONTACT, MATTE TIN TAIL.
-LM: LIGHT SELECTIVE, 10 Au / 50 Ni MIN
ON CONTACT, MATTE TIN TAIL.



CLT-111-XX-XX-D SHOWN

PACKAGING VIEW



LEAD STYLE -01
PT-1-24-01-62
TP-12

LEAD STYLE -03
PT-1-24-01-37
TP-24-02

NOTES:

- ① REPRESENTS A CRITICAL DIMENSION.
- MINIMUM PUSHOUT FORCE: .5 LB.
- PARTS TO BE SYMMETRICAL ABOUT Φ.
- WILL LOSE A POSITION FOR EVERY CUT MADE ON A SOCKET STRIP.
- PACKAGE POSITIONS -04 THRU -50 IN TUBES,
LAYER PACKAGE POSITION -02 THRU -03.
- ENDWALL AFTER CUTTING: .0215 MIN.
- C-114-22-XX CAN BE USED FOR C-114-02-XX. C-114-22-XX IS FOR
AUTOMATED ASSEMBLY PROCESSES ONLY.

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.
TOLERANCES ARE:
DECIMALS ANGLES
.XX: ±.01 [.3] 10°
.XXX: ±.005 [.13]
.XXXX: ±.0020 [.051]

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

MATERIAL: DO NOT SCALE DRAWING SHEET SCALE: 4:1
INSULATOR: LCP, UL 94 VO, COLOR: BLACK
CONTACT: PHOS BRONZE

DESCRIPTION:
2MM LOW PROFILE SOCKET STRIP

DWG. NO.
CLT-1XX-XX-XX-D

BY: PURVIS 11-02-95 SHEET 1 OF 1