

LOC		DIST		REVISIONS					
DY		-		F	LTR	DESCRIPTION	DATE	DWN	APVD
					A2	REVISED PER ECR-11-021344	20OCT2011	SYJ	LSF

1 MATERIAL:
HOUSING: HIGH TEMPERATURE PLASTIC,UL94V-0, NAT.
CONTACT: COPPER ALLOY
LATCH: SUS301 STAINLESS STEEL



2 FINISH:
CONTACT AREA: 0.00025 MIN GOLD ON
0.001 MIN ALL OVER NICKEL
SOLDERING AREA: 0.00005 MIN TO 0.00030 MAX GOLD.
LATCH: TIN.

3. TOLERANCES NON-ACCUMULATIVE.

4 PART PACKAGED IN TAPE & REEL AS PER EIA-1S704 STANDARD.
REEL DIAMETER SHALL BE 330mm,
TAPE WIDTH SHALL BE 88mm, AND
TAPE PITCH SHALL BE 36mm.

5. COMPLIES WITH JEDEC SOCKET OUTLINE SO-008.






6 DATE CODE (4-DIGITS), LOCATED AS SHOWN.
TO BE INTERPRETED AS FOLLOWS:
DIGIT # 1 - LAST DIGIT OF YEAR.
DIGITS # 2 AND # 3 - CALENDAR WEEK.
DIGIT # 4 - DAY OF THE WEEK (WITH SUNDAYS AS DAY 1).




X-1735251-1 AS SHOWN

TAPE & REEL 4	12.85	1.35	3.25	1.75	2.85	AC 1.50/1.35V (DDR3)	144	1-1735251-3
TAPE & REEL 4	13.60	2.10	2.5	2.5	2.10	AB 1.8V (DDR2)	144	1-1735251-2
SOFT TRAY	12.85	1.35	3.25	1.75	2.85	AC 1.50/1.35V (DDR3)	144	1735251-3
SOFT TRAY	13.60	2.10	2.5	2.5	2.10	AB 1.8V (DDR2)	144	1735251-2
SOFT TRAY	14.35	2.85	1.75	3.25	1.35	AA 2.5V (DDR1)	144	1735251-1
PACKAGING	DIM E	DIM D	DIM C	DIM B	DIM A	VARIATION VOLTAGE (DDR TYPE)	POS	PART NUMBER


THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. ALL ASPECTS OF THIS DRAWING, AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN: WYLEE CHK: Y.J. SEE APVD: ST. LEONG		25MAY05		TE CONNECTIVITY Singapore	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-1739		NAME S.O. DIMM SOCKET, 0.8mm PITCH, 144 POSITION, STD PROFILE	
MATERIAL		FINISH		APPLICATION SPEC 114-1114		SIZE A1	
CUSTOMER DRAWING		WEIGHT		CAGE CODE 00779		DRAWING NO C-1735251	
				SCALE 4:1		SHEET 1 of 3	
						REV A2	



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
DY	-						
			-	SEE SHEET 1	-	-	-




X-1735251-2 AS SHOWN



X-1735251-3 AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. ALL ASPECTS OF THIS DRAWING, INCLUDING THE CONTENTS AND THE ORGANIZATION, SHOULD BE CONTROLLED FOR THE LATEST REVISION.		DWN	25MAY05		 TE CONNECTIVITY Singapore	
		CHK	WYLEE			
DIMENSIONS:		APVD		NAME		
mm		Y.J. SEE				
		ST LEONG		SIZE		
		PRODUCT SPEC				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		108-1739		CAGE CODE		
		APPLICATION SPEC				
ANGLES		114-1114		DRAWING NO		
FINISH		-				
MATERIAL		WEIGHT		SCALE		
		-				
CUSTOMER DRAWING				SHEET		
				REV		
				A2		

LOC	DIST	REVISIONS			
		P	LYR	DESCRIPTION	DATE
DY	-	-	-	SEE SHEET 1	-



RECOMMENDED P.C. BOARD PATTERN LAYOUT
(CONNECTOR MOUNTING SIDE)

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. ANY DISCREPANCY TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DRN WYLEE	25MAY05	TE CONNECTIVITY Singapore	
DIMENSIONS: mm		CHK Y.J. SEE	APVD ST. LEONG	NAME S.O. DIMM SOCKET, 0.8mm PITCH, 144 POSITION, STD PROFILE	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ±0.2 4 PLC ±0.2 ANGLES ±°		PRODUCT SPEC 108-1739		APPLICATION SPEC 114-1114	
MATERIAL FINISH		WEIGHT -		SIZE A1	
CUSTOMER DRAWING		CAGE CODE 00779		DRAWING NO C-1735251	
SCALE 4:1		SHEET 3 of 3		REV A2	