



- Durable nylon cable clamps

Part Number:	CCH100-S10-C
Product Family:	Fixed Diameter Cable Clamps
Product Line:	Screw/Rivet Applied

RoHS Compliancy Status:	Compliant
-------------------------	-----------

Part Description:	Heavy Duty Fixed Diameter Cable Clamp
-------------------	---------------------------------------

Product Type:	Mounting Device
---------------	-----------------

Material:	Nylon 6.6
-----------	-----------

Color:	Natural
--------	---------

UL Recognized:	E136577
----------------	---------

Diameter (In.):	.20
-----------------	-----

Diameter (mm):	5.1
----------------	-----

Width (In.):	.50
--------------	-----

Width (mm):	12.7
-------------	------

Bundle Offset (mm):	23.1
Bundle Offset (In.):	.91
Environment:	Indoors
Flammability Rating:	UL94 V-2
Hole Diameter (In.):	.20
Hole Diameter (mm):	5.1
Max. Bundle Diameter (In.):	1.00
Max. Bundle Diameter (mm):	25.4
Metric Screw Size:	M5
Mounting Method:	#10 (M5) Screw
Screw Size:	#10 (M5)
Std. Pkg. UOM:	PK
Type Of Application:	Heavy Duty
UOM:	PC
Std. Pkg. Qty.:	100
Min. Order Qty.:	100