


DESCRIPTION: MALE - HIGH DENSITY - MACHINED CONTACTS - RIGHT ANGLE



MATERIAL:

- SHELL: STEEL MATERIAL, NICKEL FINISH
- INSULATOR: PA6T=260°C, UL 94V-0 RATED, BLACK
- CONTACT MATERIAL: BRASS
- CONTACT FINISH: SELECTIVE GOLD FINISHED
- SEALING MATERIAL: F08 FLEXIBLE ADHESIVE

ELECTRICAL:

- CONTACT CURRENT RATING: 5 AMPS
- CONTACT RESISTANCE: 30 Milliohms Max.
- DIELECTRIC WITHSTANDING VOLTAGE: 1,000VAC Min.
- INSULATION RESISTANCE: 5,000 Megohms Min.
- TEMPERATURE RATING: -55° ~ +105° C

781-M YY-1 1 3 R YY 1

SERIES _____

MACHINED CONTACTS _____

POSITIONS _____

15 _____

26 _____

44 _____

GENDER _____

1 = MALE _____

TERMINATION _____

1 = RIGHT ANGLE _____

SHELL PLATING _____

3 = NICKEL _____

RoHS COMPLIANT _____

HARDWARE OPTIONS _____

00 = NO HARDWARE _____

14 = BRACKET WITH #4-40 INSERT, BOARD LOCK & LOCATOR PLATE _____

PLATING OPTIONS _____

1 = GOLD FLASH, ENTIRE CONTACT _____


DIMENSIONS (IN.)				
No. OF PINS	A	B	C	D
15	1.213	0.984	0.666	0.759
26	1.541	1.312	0.994	1.083
44	2.088	1.852	1.534	1.625

MEETS IP67 STANDARDS
(SEE PAGE 4 FOR SEALING DETAILS)

DO NOT SCALE FROM DRAWING


	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.		DRAWN: C. SMITH		DATE: 03-16-07					
			CHECKED:		DATE:					
			SCALE: 1 : 1	SHEET 1 OF 4	REV 2					
NorComp			DWG NO. 781-MYY-113RYY1							

RoHS COMPLIANT



MOUNTING BRACKET
WITH BOARD LOCK

HARDWARE OPTION 14






BRACKETS MOUNTED ON CONNECTOR
WITH LOCATOR PLATE

HARDWARE OPTION 14

FOR CLARITY
HIDDEN LINES
NOT SHOWN

MATERIAL: COLD ROLLED STEEL
PLATING: CLEAR ZINC


	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: PAM JENKINS		DATE: 11-28-05	
		CHECKED:		DATE:	
	SCALE: 1 : 1		SHEET 2		OF 4
	DWG NO. 781-MYY-113RYY1				
REV 2					



*** TYP. ON ALL SIZES**

DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: C. SMITH		DATE: 03-16-07	
		CHECKED:		DATE:	
NorComp		SCALE: 1 : 1		SHEET 3 OF 4	
		REV 2		DWG NO. 781-MYY-113RYY1	



DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: C. SMITH		DATE: 06-10-09	
		CHECKED:		DATE:	
NorComp	SCALE: 2.5 : 1		SHEET 4 OF 4		REV 2
	DWG NO. 781-MYY-113RYY1				