

Thermofit[®] Molded Parts
Specification Control Drawing
Limited Distribution

Part Number : 222F242-XX-02
Description : Boot, 90°, With Lip

NOTES

1. All dimensions are in

inches

millimeters
2. Dimensions appearing in table are as follows:

a - As Supplied

b - After Unrestricted Recovery
3. Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by .06 max.
4. "S" & "T" dimensions apply to a minimum of 240° of the circumference.




TABLE OF DIMENSIONS										
PART NUMBER	H		J		P	R	HW	JW	S	T
	Min	Max	Min	Max	±10%	±10%	+.06 -.03	±.03	+.06 -.03	±.03
	a	b	a	b	b	b	b	b	b	b
222F242-XX-02	1.40 [35,6]	.87 [22,1]	1.13 [28,7]	.40 [10,2]	3.10 [78,7]	.86 [21,8]	.07 [1,78]	.06 [1,52]	.07 [1,78]	.05 [1,3]

Raychem

RAYCHEM CORPORATION
300 CONSTITUTION DRIVE
MENLO PARK, CALIFORNIA 94025

Revision : A
Date : 4/16/97

Part Number : 222F242-XX-02
Description : Boot, 90°, With Lip

Thermofit[®] Molded Parts
Specification Control Drawing
Limited Distribution

Part Number : 222F242-XX-02
Description : Boot, 90°, With Lip

COMPATABILITY CHART					
MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.	COATING DESCRIPTION
-51	Flexible EPB	RT-1321	/164	S-1124	Adhesive

ORDERING INFORMATION

222F242

-51

-02

/164

Base part number

Material dash number
(See Compatability Chart)

Modification number
(If necessary, see front of scd binder for a complete list)

Adhesive slash number
(If necessary, see Compatability Chart)

THIS DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE; CONSULT YOUR
NEAREST FIELD REPRESENTATIVE FOR CURRENT REVISION

If this document is printed it becomes uncontrolled.
Check for the latest revision.

Raychem

RAYCHEM CORPORATION
300 CONSTITUTION DRIVE
MENLO PARK, CALIFORNIA 94025

Revision : A
Date : 4/16/97

Part Number : 222F242-XX-02
Description : Boot, 90°, With lip