







## Female headers

### Stamped contact spring (fork contact)







– **separable!** any requested number of contact can be delivered

– for □ 0.635 mm pin cross section, straight

|                                                                    |                                                                                                                                                                                                                                                                                                                                            |
|--------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>art. no.</b><br><br><br><br><br><br><br><br><br><b>BL 1 ...</b> |     |
| <b>art. no.</b><br><br><br><br><br><br><br><br><br><b>BL 2 ...</b> |     |
| <b>please indicate:</b>                                            | <div> <div>... no. of contacts</div> <div>one row 1 - 36</div> <div>two rows 2 - 72</div> </div> <div> <div>... surface of contact</div> <div>G = gold-plated</div> <div>Z = tin-plated</div> </div>                                                                                                                                       |

– for □ 0.635 mm pin cross section, angled

– **BL 4 ...:** packing (option) bar magazine (≥6 contacts)

|                                                                    |                                                                                                                                                                                                                                                                                                                                                    |
|--------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>art. no.</b><br><br><br><br><br><br><br><br><br><b>BL 3 ...</b> |     |
| <b>art. no.</b><br><br><br><br><br><br><br><br><br><b>BL 4 ...</b> |     |
| <b>please indicate:</b>                                            | <div> <div>... no. of contacts</div> <div>one row 1 - 36</div> <div>two rows 2 - 72</div> </div> <div> <div>... surface of contact</div> <div>G = gold-plated</div> <div>Z = tin-plated</div> </div>                                                                                                                                               |