



English | 简体中文 | 日本語

Search by Part Number

GO

Search Site by keyword

GO

Contact IDT | Investors | Press

About IDT

Products

Applications

Support

myIDT

Calculators | Cross Reference | Green Initiative | Military | Parametric Search | Search by Part Number, Keyword, Document, Green/Pb-Free, Package

Home > Products > > 960010 > 960010AFLF

You may also like...

960010AFLF

Category:

Generic Part: 960010

Market Group: PC CLOCK

Description: PC SPECIAL PURPOSE

Features:

- CPU, ASIC, and PCI can run at 2.5V or 3.3V selectable.
- 1-CPU (2.5V/3.3V) (66.66MHz to 100.00MHz)
- 2-PCI (2.5V/3.3V) (33.33MHz)
- 2-ASIC (2.5V/3.3V) (66.66MHz to 100.00MHz)
- 1-ASIC (2.5V/3.3V) (33.33MHz to 100.00MHz)
- 1-12MHz (3.3V)

Time is money

Parameters

Speed	NA
Temperature	C
Voltage	3.3 V
Status	Active
Sample	Yes
Minimum Order Quantity	141
Factory Order Increment	47

Distributor Inventory

No Pricing information is available from our Distributors at this time.

Documents

Type	Title	Size	Revision Date
Misc	PC Clocks Contact Info	61 KB	05/29/2007

Package

Package	SSOP 28 (PYG28)
Description	SSOP 5.3 MM
Status	Active
Class	PLASTIC
Category	Green
Pb (Lead) Free	Yes
Mark	F
Package Type	SSOP
Lead Count	28
Length	10.2 mm
Width	5.3 mm
Thickness	1.73 mm
Pitch	0.65 mm
Tube / Tray	TUBE
Quantity per Tube/Tray	47
Quantity per Reel	1000
Moisture Sensitivity Level (MSL)	1
Moisture Exposure Floor Life	Unlimited@<30C/85% RH
Peak Reflow Temperature	260Â°C
Rebake Conditions	NA
Related Package Documents	view documents

[Home](#) | [Site Map](#) | [Legal](#) | [Careers](#) | [Contact Us](#) | [Quality](#) | [RSS](#) [What is this?](#)

Use of this website signifies your agreement to the [acceptable use](#) and [privacy policy](#). Copyright © 1997-2008 Integrated Device Technology, Inc. [All Rights Reserved](#).