

North America: Danboro, PA • E-mail: info@pemnet.com • Tel: +1-215-766-8853
Europe: Galway, Ireland • E-mail: europe@pemnet.com • Tel: +353-91-751714
Asia/Pacific: Singapore • E-mail: singapore@pemnet.com • Tel: +65-6-745-0660
 Shanghai, China • E-mail: china@pemnet.com • Tel: +86-21-5868-3688

Part # AELS8-1032-130, Low profile head – Open End - Unified

- Feature a large diameter, low-profile head and knurled shank.
- Offers highest all around strength.



Type	Threads	Standard Material	Standard Finish
AELS / AENS	Unified, 18 per A/CAN, 812 Metric, 18 per A/ISO, 812/88	Low Carbon Steel	Hot-Dip Coated Zinc Yellow Plus Lubricant
AELS / AENS	Unified, 18 per A/CAN, 812 Metric, 18 per A/ISO, 812/88	Stainless Steel	Passivated and/or treated per ASTM A308
AELS / AENS	Unified, 18 per A/CAN, 812 Metric, 18 per A/ISO, 812/88	Aluminum	No Finish
AELS / AENS	Unified, 18 per A/CAN, 812 Metric, 18 per A/ISO, 812/88	Brass	No Finish


Specifications

Thread Size #10-32

Grip Range .020 - .130 in

A ± .015 .475 in

B ± .015 .415 in



C Nom. .030 in

ØD Max. .296 in

M Ref. .315 in

Hole Size in Sheet + 0.006 - 0.000 .297 in

Fastening	Uninstalled
Thread Specification	2B per ASME B1.1
Standard Material	Low Carbon Steel
Standard Finish	RoHS Compliant Zinc Yellow Plus Lubricant
CAD Supplier	PennEngineering® (Atlas®)