


REV.	DATE	DESCRIPTION
NC	12/18/98	INITIAL RELEASE
A	10/30/07	UPDATE DRAWING FORMAT, REVISE BODY PLATING TO NEXCOTE



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	Amphenol Connex			
8						DRAWN G.R.S.	10/30/07				
7					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:	CHECKED		PART DESCRIPTION			
6					0.5 - 8mm ± 0.20mm	ISSUED					
5					8 - 30mm ± 0.40mm	SHEET 1 OF 1		N "T" ADAPTER JACK-JACK-PLUG			
4					30 - 120mm ± 0.50mm						
3	CONTACT PIN	PHOS. BRONZE	GOLD	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:			PART NO. 172233			
2	INSULATOR	TEFLON	NATURAL	1	.020 - .315 = ± 0.007"						
1	BODY	BRASS	NEXCOTE	1	.315 - 1.180 = ± 0.015"			DWG. NO. 172233.DWG			
	DESCRIPTION	MATERIAL	FINISH	QTY	1.180 - 4.724 = ± 0.020"						
					DO NOT SCALE DRAWING	CAD FILE C:/172/172233.DWG		REV. A	SIZE A	SCALE NA	